

Euclid™ Pendants and Pushbuttons

2015/16/17

Price List 2015 • January 2015, Replaces May 2013

Type PBC Enclosure Discount Code EA

NEMA Type 1 Enclosure

Length	Without Space For Toggle Switch			With Space For Toggle Switch		
	Cat. No.	Part No.	List Price	Cat. No.	Part No.	List Price
4 Buttons	C2	28578-002	\$822	CT2	65012-002	\$832
6 Buttons	C3	28578-003	\$906	CT3	65012-003	\$942
8 Buttons	C4	28578-004	\$991	CT4	65012-004	\$1062
10 Buttons	C5	28578-005	\$1260	CT5	65012-005	\$1345
12 Buttons	C6	28578-006	\$1593	CT6	65012-006	\$1678

Ordering Instructions

Total price of an assembled pushbutton station is obtained by adding the enclosure price and pushbutton insert prices plus pricing for any special nameplate markings require. Standard nameplate markings are included in enclosed price.

Example Catalog No. PBC-P1R135T

Qty.	Cat. No.	Description	List Price
1	CT4	8 Button 7 Toggle Enclosure	\$1062
1	P1	110 VAC Pilot Light Marked: Power On	\$407
1	R	Reset Button Marked: Reset	\$163
1	A1	Single Speed Mrkd: Fwd-Bridge-Rev	\$255
1	A3	Three Speed Mrkd: Fwd-Trolley-Rev	\$358
1	A5	Five Speed Mrkd: Up-Hoist-Down	\$485
1	T	Toggle Switch Marked: Off-On	\$581

Total List Price \$3311
Refer to your local sales office for special inserts or features.

Type WPBC Enclosure Discount Code EA

NEMA Type 3R¹/13 Enclosure

Length	Type WPBC Pendant Mounted			Type SWPBC Surface Mounted		
	Cat. No.	Part No.	List Price	Cat. No.	Part No.	List Price
2 Buttons	WC1	28581-001	\$730	SWC1	28581-301	\$1154
4 Buttons	WC2	28581-002	\$899	SWC2	28581-302	\$1402
6 Buttons	WC3	28581-003	\$1133	SWC3	28581-303	\$1678
8 Buttons	WC4	28581-004	\$1388	SWC4	28581-304	\$2025
10 Buttons	WC5	28581-005	\$1664	SWC5	28581-305	\$2414
12 Buttons	WC6	28581-006	\$2004	SWC6	28581-306	\$2832
14 Buttons	WC7	28581-007	\$2351	SWC7	28581-307	\$3313

¹ For NEMA 4 constructions add \$361 list and specify voltage for internal space heater

Type XPBC Enclosure Discount Code EF

NEMA Type 7 Class 1, Group C or D, Div. 1 or 2 enclosure for indoor applications and NEMA Type 9, Class 2, Group E, F or G, Div. 1 or 2 enclosures for indoor applications.

Length	Type XPBC Pendant Mounted			Type 2XPBC Duplex Pendant Mounted			Type SXPBC Surface Mounted		
	Cat. No.	Part No.	List Price	Cat. No.	Part No.	List Price	Cat. No.	Part No.	List Price
2 Buttons	XC1	28595-301	\$1598	12 Buttons	2XC3	\$6556	SXC1	28595-306	\$1723
4 Buttons	XC2	28595-302	\$2366	16 Buttons	2XC4	\$8092	SXC2	28595-307	\$2491
6 Buttons	XC3	28595-303	\$3134	20 Buttons	2XC5	\$13400	SXC3	28595-308	\$3259
8 Buttons	XC4	28595-304	\$3902				SXC4	28595-309	\$4027
10 Buttons	XC5	28595-305	\$4670				SXC5	28595-310	\$4796

Standard Nameplate Marking²

Up	Raise	East	On	Open	Lift	Reset	Hoist	Main Hoist
Down	Lower	West	Off	Close	Drop	Inch	Bridge	Aux. Hoist
Fwd	Left	North	Start	Fast	In	Run	Trolley	Magnet
Rev	Right	South	Stop	Slow	Out	Jog	Crane	Power On ³

² Specify nameplate marking arrangement. Add \$47 each for special nameplate markings not listed.

³ Standard marking for pilot light only.



Standard Pushbutton Inserts

Description	Type PBC Disc Code EA			Type WPBC Disc Code EA			Type XPBC Disc Code EF		
	Cat. No.	Part No.	List Price	Cat. No.	Part No.	List Price	Cat. No.	Part. No.	List Price
Start - Stop	A1A	54601-145	\$255	A1A	54601-145	\$255	X1A	74601-145	\$308
Stop-Start	A1C	54601-148	\$255	A1C	54601-148	\$255	X1C	74601-148	\$308
Single Speed	A1	54601-023	\$255	A1	54601-023	\$255	X1	74601-023	\$308
Two Speed	A2	54602-002	\$358	A2	54602-002	\$358	X2	74602-002	\$411
Three Speed	A3	54603-001	\$358	A3	54603-001	\$358	X3	74603-001	\$411
Four Speed	A4	54604-001	\$485	A4	54604-001	\$485	X4	74604-001	\$538
Five Speed	A5	54605-001	\$485	A5	54605-001	\$485	X5	74605-001	\$538
120 VAC Pilot Light	P1	54698-001	\$407	P1	54698-001	\$407	XP1	74698-001	\$676
250 VDC Pilot Light	P5	54698-005	\$407	P5	54698-005	\$407	XP5	74698-005	\$676
30A 2-Pole Toggle Switch	T	28484-100	\$581	WT*	28436-102	\$581	XT*	28436-103	\$1780
Reset Button	R	54691-150	\$163	R	54691-150	\$163	XR	74691-150	\$190
Maintained Type On-Off	M	54601-036	\$358	M	54601-036	\$358	XM	74601-036	\$411

*"Off-On" toggle switch or pushbutton recommended to comply with provisions of NEMA ICS 3-422.15. Consult factory for special contact sequences. Requests must include sequence of operation and nameplate markings. ***Note: WT and XT Toggles require two button spaces.**

Special Pushbutton Inserts

Description	Type PBC Disc Code EA			Type WPBC Disc Code EA			Type XPBC Disc Code EF		
	Cat. No.	Part No.	List Price	Cat. No.	Part No.	List Price	Cat. No.	Part. No.	List Price
Alarm Button	A1-22	54691-022	\$163	A1-22	54691-022	\$163	X1-22	74691-022	\$190
Lift/Drop - Magnet	A1-37	54601-037	\$425	A1-37	54601-037	\$425	X1-37	74601-370	\$478
2 Speed with Overlapping Contacts	A2-3	54602-003	\$358	A2-3	54602-003	\$358	X2-3	74602-003	\$411
Std. 3 Speed with LV (N/C) Circuit	A3-6	54603-006	\$485	A3-6	54603-006	\$485	A3-6	74603-006	\$538
Std. 3 Speed with LV (N/C) & M (N/O) Circuits	A3-12	54603-012	\$612	A3-12	54603-012	\$612	A3-12	74603-012	\$666
4 Speed/Dynamic Lowering - Std. 4121 Hoist	A4-90	54604-090	\$612	A4-90	54604-090	\$612	A4-90	74604-090	\$666
Std. 4 Speed with LV & M Circuits - Std. 4120 Travel	A4-7	54604-007	\$612	A4-7	54604-007	\$612	A4-7	74604-007	\$666
Std. 5 Speed with LV Circuit - Std. 4120 Travel	A5-6	54605-006	\$612	A5-6	54605-006	\$612	A5-6	74605-006	\$666
Std. 5 Speed with LV & M Circuits - Std. 4110 Travel	A5-13	54605-013	\$750	A5-13	54605-013	\$750	A5-13	74605-013	\$804
5 Speed/Dynamic Lowering - Std. 4111 Hoist	A5-380	54605-380	\$750	A5-380	54605-380	\$750	A5-380	74605-380	\$804

Price Additions for Modifications

Standard modifications of PBC, WPBC & XPBC Pushbutton Stations. Order by modification number and complete specifications.

Description	Type PBC Disc Code EA		Type WPBC Disc Code EA		Type XPBC Disc Code EF	
	Mod. No.	List Price	Mod. No.	List Price	Mod. No.	List Price
Mounting Two Stations Together, Side-By-Side, Including Duplex Tie Straps	M1	\$212	M9	\$212	See 2XPBC	
Additions of U-Shaped Handle to Bottom Tie Strap	M2	\$347	M10	\$347	M17	\$347
Top Interconnecting Conduit Box for Duplex Station with One Top Conduit Fitting (1-1/2"), also with Duplex Tie Strap	M3	\$2000	M11	\$2124	---	N/A
Addition of Vertical Side Handles to a Single or Duplex Station	M4	\$372	M12	\$372	M18	\$559
Addition of Complete Circular Guard to Pushbutton Operator	M5	\$372	M13	\$248	---	N/A
Addition of Standard 1-5/8" Diameter Mushroom Head to Pushbutton Operator	M6	\$74	M14	\$74	M21	\$74
Addition to "W" Wobble Stick to Bottom of Single Station	M7	\$736	M15	\$981	---	N/A
Addition of Euclid 2 or 3 Position Selector Switch to Std. Station Including Nameplate	M8	\$559	M16	\$772	M22	\$988
Double Potentiometer Stepless Insert*	M19D	\$3540	M20D	\$3540	M24D	\$3593
Single Potentiometer Stepless Insert*	M19S	\$2301	M20S	\$2301	M24S	\$2354

Note: For modifications not shown, refer to your local sales office or the factory. *Furnish complete specifications..



Hubbell Industrial Controls, Inc.

a subsidiary of Hubbell Incorporated
 4301 Cheyenne Drive, Archdale, NC 27263
 Phone (336) 434-2800 | Fax (336) 434-2801
 www.hubbell-icd.com
 sales@hubbell-icd.com