



**Commercial, Industrial
and Residential Electrical Products**

Meet code with Steel EMT Compression Fittings for Wet Locations

Quality Raintight Fittings

Application

Use RACO Raintight Steel EMT Compression Fittings in wet locations to bond and secure EMT conduit to a box, enclosure, or couple two ends of EMT conduit. RACO Raintight Steel EMT Compression Fittings have been designed to comply with the new U.L. Raintight test requirements and to comply with the requirements of the 2008 NEC 358.42 and 314.15

Features

- All steel construction ensures mechanical protection for the raceway
- Fittings are available in 1/2" to 4" trade sizes. RACO offers one of the most complete lines in the industry
- Zinc Electroplate Finish provides for a durable, corrosion resistant installation
- Blue tinted compression nuts and "Wet Locations" markings allow inspecting authorities to immediately determine that the installation is up to code
- All connectors are supplied with a factory installed knockout seal. No need to add the expense of buying a gasket separately
- No need to disassemble the fitting prior to installation. RACO Raintight Steel EMT Compression Fittings are designed so that when they come out of the carton they can be installed directly on the conduit. No need to waste time loosening compression nuts
- No need for special tools to install properly. Install these fittings like any other steel EMT compression fitting. No need for torque wrench to insure proper installation



2902RT



2912RT



2922RT



2928RT



INSULATED CATALOG #	UNINSULATED CATALOG #	TRADE SIZE	UNIT CTN. QTY.	SHIP CTN. QTY.	BAR CODE
Compression Connectors, Raintight – Steel					
2912RT	2902RT	1/2"	50	250	—
2913RT	2903RT	3/4"	25	125	—
2914RT	2904RT	1"	15	75	—
2915RT	2905RT	1-1/4"	—	20	—
2916RT	2906RT	1-1/2"	—	10	—
2918RT	2908RT	2"	—	10	—
2960RT	2940RT	2-1/2"	—	1	—
2962RT	2942RT	3"	—	1	—
2964RT	2944RT	3-1/2"	—	1	—
2966RT	2946RT	4"	—	1	—

CATALOG #	TRADE SIZE	UNIT CTN. QTY.	SHIP CTN. QTY.	BAR CODE
Compression Couplings, Raintight – Steel				
2922RT	1/2"	50	250	—
2923RT	3/4"	25	125	—
2924RT	1"	15	75	—
2925RT	1-1/4"	—	20	—
2926RT	1-1/2"	—	10	—
2928RT	2"	—	10	—
2950RT	2-1/2"	—	1	—
2952RT	3"	—	1	—
2954RT	3-1/2"	—	1	—
2956RT	4"	—	1	—



**COMMERCIAL
CONSTRUCTION**
A Division of Hubbell Incorporated (Delaware)

RACO
3902 W. Sample St.
South Bend, IN 46619
574-234-7151
www.hubbell.com/raco/en

