



CONDUIT HANGERS WITH BOLT AND THREADED HOLE



Threaded hole eliminates need for a nut

Application

RACO conduit hangers are suitable for use in wet or dry locations to support runs of Rigid/IMC and EMT conduit from ceilings and walls.

Features

- Hangers are supplied with a retained bolt and threaded hole eliminating the need for a nut
- Multi-directional mounting either vertically from the ceiling, or horizontally on a wall
- Durable steel construction with a pre-galvanized finish for corrosion protection
- Sizes available for 3/8" to 2" Rigid/IMC conduit, and 1/2" to 2" EMT conduit
- All sizes are compliant with UL and cULus standards for your safety and peace of mind

Catalog No.	Description	Trade Size	Rigid/IMC Size	EMT Size	Ship Ct. Qty.	Wght. Lbs. per 100	Carton Dims. L x W x H	Carton 1 of 5
2052TH	# 0TS 3/8" - 1/2" RGD 1/2" EMT	0	1/2"	1/2"	100	6.2	7 x 5.2 x 3.4	50050169911902
2053TH	# 1TS 3/4" RGD/EMT	1	3/4"	3/4"	100	6.6	6.7 x 6.7 x 6.1	50050169911919
2054TH	# 2TS 1" RGD/EMT	2	1"	1"	100	8.4	10.6 x 10.4 x 3.5	50050169911926
2041TH	# 2-1/2TS 1-1/4" EMT	2-1/2	-	1-1/4"	100	10.2	10.4 x 10.4 x 10.8	50050169911933
2055TH	# 3TS 1-1/4" RGD 1-1/2" EMT	3	1-1/4"	1-1/2"	100	14.2	10.4 x 10.4 x 10.8	50050169911940
2056TH	# 4TS 1-1/2" RGD	4	1-1/2"	-	100	15.1	13.6 x 9.7 x 6.7	50050169911957
2058TH	# 5TS 2" RGD/EMT	5	2"	2"	50	16.9	10.6 x 10.4 x 4.8	50050169911964