



## RACO® COLOR-CODED CORD GRIP CONNECTORS

### Application

For use in wet or dry locations to provide a liquidtight and strain relief termination for flexible cord and cable. RACO liquidtight strain relief cord connectors are suitable for use in Class I, Div. 2, Class II, Div. I and 2; Class III, Div. I and 2 hazardous locations.

### Features

- Straight connectors are available in steel; 45° and 90° connectors available in malleable iron
- Neoprene grommets are color-coded by cable diameter allowing for quick and easy identification
- Steel and malleable iron construction provides mechanical strength and durability
- Metallic components are zinc plated for corrosion protection
- Unique grommet design is forced up and around the cord when the nut is tightened creating a liquidtight seal
- Time saving and easy installation - no need to disassemble the fitting for cord installation

### Compliances

- cUL<sub>us</sub>
- NEMA 4

DIAMETER RANGE - MIN. - MAX. (IN.)	COLOR CODE
.15 - .25	Red
.25 - .35	White
.35 - .45	Blue
.45 - .56	Green
.55 - .65	Brown
.65 - .75	Yellow
.75 - .85	Purple
.85 - .95	Gray
.95 - 1.05	Black
1.05 - 1.15	Orange
1.15 - 1.25	Red
1.25 - 1.375	White

### 90 DEGREE CONNECTORS

Catalog Number	Trade Size	Grommet Color	Cable Range (In.)	Ship Ctn. Qty.	UPC	Carton Size (In.)	Carton 1 2 of 5	Carton Wght. (Lbs)
3794-0	1/2"	Red	.15 -.25	25	050169983249	6x6x4	50050169983244	7.3
3794-1	1/2"	White	.25 -.35	25	050169983256	6x6x4	50050169983251	7.4
3794-2	1/2"	Blue	.35 -.45	25	050169983263	6x6x4	50050169983268	7.25
3794-3	1/2"	Green	.45 -.56	25	050169983270	6x6x4	50050169983275	7.25
3794-4	1/2"	Brown	.55 -.65	25	050169983287	6x6x4	50050169983282	7.13
3795-0	3/4"	Red	.15 -.25	10	050169983294	6x6x6	50050169983299	4.64
3795-1	3/4"	White	.25 -.35	10	050169983300	6x6x6	50050169983305	4.83
3795-2	3/4"	Blue	.35 -.45	10	050169983317	6x6x6	50050169983312	4.54
3795-3	3/4"	Green	.45 -.56	10	050169983324	6x6x6	50050169983329	4.53
3795-4	3/4"	Brown	.55 -.65	10	050169983331	6x6x6	50050169983336	4.57
3795-5	3/4"	Yellow	.65 -.75	10	050169983348	6x6x6	50050169983343	4.57
3795-6	3/4"	Purple	.75 -.85	10	050169983355	6x6x4	50050169983350	4.27
3796-0	1"	Green	.45 -.56	10	050169983362	6x6x4	50050169983367	6.61
3796-1	1"	Brown	.55 -.65	10	050169983379	6x6x4	50050169983374	6.78
3796-2	1"	Yellow	.65 -.75	10	050169983386	6x6x4	50050169983381	6.57
3796-3	1"	Purple	.75 -.85	10	050169983393	6x6x4	50050169983398	6.37
3796-4	1"	Gray	.85 -.95	10	050169983409	6x6x4	50050169983404	7.13
3796-5	1"	Black	.95 -1.05	10	050169983416	6x6x4	50050169983411	7.09

## 45 DEGREE CONNECTORS

Catalog Number	Trade Size	Grommet Color	Cable Range (In.)	Ship Ctn. Qty.	UPC	Carton Size (In.)	Carton 1 2 of 5	Carton Wght. (Lbs)
3745-0	1/2"	Red	.15 -.25	25	050169983423	6x6x4	50050169983428	6.78
3745-1	1/2"	White	.25 -.35	25	050169983430	6x6x4	50050169983435	6.73
3745-2	1/2"	Blue	.35 -.45	25	050169983447	6x6x4	50050169983442	6.75
3745-3	1/2"	Green	.45 -.56	25	050169983454	6x6x4	50050169983459	6.58
3745-4	1/2"	Brown	.55 -.65	25	050169983461	6x6x4	50050169983466	6.55
3746-0	3/4"	Red	.15 -.25	10	050169983478	6x6x4	50050169983473	4.2
3746-1	3/4"	White	.25 -.35	10	050169983485	6x6x4	50050169983480	4.25
3746-2	3/4"	Blue	.35 -.45	10	050169983492	6x6x4	50050169983497	4.18
3746-3	3/4"	Green	.45 -.56	10	050169983508	6x6x4	50050169983503	4.18
3746-4	3/4"	Brown	.55 -.65	10	050169983515	6x6x4	50050169983510	4.12
3746-5	3/4"	Yellow	.65 -.75	10	050169983522	6x6x4	50050169983527	3.76
3746-6	3/4"	Purple	.75 -.85	10	050169983539	6x6x4	50050169983534	3.72
3747-0	1"	Green	.45 -.56	10	050169983546	6x6x4	50050169983541	5.51
3747-1	1"	Brown	.55 -.65	10	050169983553	6x6x4	50050169983558	5.56
3747-2	1"	Yellow	.65 -.75	10	050169983560	6x6x4	50050169983565	5.44
3747-3	1"	Purple	.75 -.85	10	050169983577	6x6x4	50050169983572	5.38
3747-4	1"	Gray	.85 -.95	10	050169983584	6x6x4	50050169983589	6.31
3747-5	1"	Black	.95 -1.05	10	050169983591	6x6x4	50050169983596	6.21

## STRAIGHT CONNECTORS

Catalog Number	Trade Size	Grommet Color	Cable Range (In.)	Ship Ctn. Qty.	UPC	Carton Size (In.)	Carton 1 2 of 5	Carton Wght. (Lbs)
3722-0	1/2"	Red	.15-.25	25	050169982969	6x6x4	50050169982964	3.08
3722-1	1/2"	White	.25-.35	25	050169982976	6x6x4	50050169982971	3
3722-2	1/2"	Blue	.35-.45	25	050169982983	6x6x4	50050169982988	2.98
3722-3	1/2"	Green	.45-.56	25	050169982990	6x6x4	50050169982995	2.95
3722-4	1/2"	Brown	.55-.65	25	050169983003	6x6x4	50050169983008	2.83
3723-0	3/4"	Red	.15-.25	25	050169983010	6x6x4	50050169983015	4.50
3723-1	3/4"	White	.25-.35	25	050169983027	6x6x4	50050169983022	4.50
3723-2	3/4"	Blue	.35-.45	25	050169983034	6x6x4	50050169983039	4.45
3723-3	3/4"	Green	.45-.56	25	050169983041	6x6x4	50050169983046	4.35
3723-4	3/4"	Brown	.55-.65	25	050169983058	6x6x4	50050169983053	4.25
3723-6	3/4"	Yellow	.65-.75	25	050169983065	6x6x4	50050169983066	4.58
3723-5	3/4"	Purple	.75-.85	25	050169983072	6x6x4	50050169983077	4.53
3724-0	1"	Green	.45-.56	25	050169983089	6x6x6	50050169983084	7.03
3724-1	1"	Brown	.55-.65	25	050169983096	6x6x6	50050169983091	7.08
3724-5	1"	Yellow	.65-.75	25	050169983102	6x6x6	50050169983107	6.85
3724-2	1"	Purple	.75-.85	25	050169983119	6x6x6	50050169983114	6.88
3724-3	1"	Gray	.85-.95	25	050169983126	6x6x6	50050169983121	7.23
3724-4	1"	Black	.95-1.05	25	050169983133	6x6x6	50050169983138	7.15
3725-0	1-1/4"	Purple	.75-.85	25	050169983140	6x6x6	50050169983145	11.30
3725-1	1-1/4"	Gray	.85-.95	25	050169983157	6x6x6	50050169983152	11.23
3725-2	1-1/4"	Black	.95-1.05	25	050169983164	6x6x6	50050169983169	11.25
3725-4	1-1/4"	Orange	1.05-1.15	25	050169983171	6x6x6	50050169983176	11.70
3725-5	1-1/4"	Red	1.15-1.25	25	050169983188	6x6x6	50050169983183	11.33
3725-3	1-1/4"	White	1.25-1.375	25	050169983195	6x6x6	50050169983190	11.13
3726-0	1-1/2"	Black	.95-1.05	25	050169983201	9x7x5	50050169983206	17.63
3726-1	1-1/2"	Orange	1.05-1.15	25	050169983218	9x7x5	50050169983213	17.45
3726-2	1-1/2"	Red	1.15-1.25	10	050169983225	6x6x4	50050169983220	6.96
3726-3	1-1/2"	White	1.25-1.375	10	050169983232	6x6x4	50050169983237	6.84