



*Commercial, Industrial
and Residential Electrical Products*

NEW!
IMPROVED



Save Time and Effort! Push-in Cable Connectors



38RAC



40RAC

Rugged one-piece design provides fast tool-free install!

Applications

RACO's new *Push-in* cable connectors make it easy to secure metal-clad cable into boxes or enclosures. Simply insert a cable into the cable opening, then snap the box end of the connector into a box knockout, done! No tools needed for a secure assembly. *Push-in* connectors are perfect for new or old work and can be removed and reused.

Features

- Fits standard 1/2" knockouts in electrical boxes or enclosures
- Both connectors designed to terminate MC-PCS, MCI, MCI-A, AC, HCF, and FMC
- 40RAC tinted blue inside to indicate larger cable range
- Die-cast zinc construction with nylon anti-short bushing
- For use in dry locations
- See back for cable size ranges



Catalog No.	Description	Unit Carton Qty.	Inner Carton Qty.	Ship Carton Qty.	Carton 1 of 5
38RAC	3/8" Push-in Connector (1/2" KO)	50	30050160000381	500	50050169000385
40RAC	3/8" Push-in Connector (1/2" KO)	50	30050169000404	500	50050169000408

38RAC

CABLE TYPE (Steel & Aluminum)	CABLE RANGES
MC	14/2 - 10/3
MCI-A	
AC/HCF	
MCI-A HCF	12/2 - 10/3
MC-PCS (SOLID)	12/2 - 12/3
RWFMC CONDUIT	3/8" TRADE SIZE FLEX Anti Short Bushing Required

Cable Diameter Range: 0.402" - 0.610"

40RAC

CABLE TYPE (Steel & Aluminum)	CABLE RANGES
MC	14/3 - 10/3
MCI-A	
AC	
AC HCF	14/2 - 10/3
MCI-A HCF	12/2 - 10/3
MC-PCS (SOLID)	12/2 - 12/3
RWFMC CONDUIT	3/8" TRADE SIZE FLEX Anti Short Bushing Required

Cable Diameter Range: 0.470" - 0.610"

38RAC/40RAC CONNECTOR REMOVAL INSTRUCTIONS

