

Wiegmann now offers product that is approved by NEMA and IEC. The following products now carry an IEC IP66 rating along with a NEMA rating.

JIC LIFT OFF CLAMP COVER	JIC CONTINUOUS HINGE CLAMP COVER	JIC CONTINUOUS HINGE QTR TURN LATCH
BN4	BN4_CH	BN4_CHQT
BN4_AL	BN4_CHAL	BN4_CHQTSS
BN4_SS	BN4_CHSS	BN4_CHQTSSA
BN4_SSA	BN4_CHSSA	

SINGLE DOOR	SINGLE DOOR WITH WINDOW	SINGLE DOOR SLOPE TOP
N412_C	N412_WC	N412_CST
N412_SSC	N412_WSSC	N412_CSSST
N412_SSAC	<b>SINGLE DOOR DISCONNECT</b>	<b>SINGLE DOOR SLOPE TOP DISCONNECT</b>
N412_3PTC		
N412_SS3PTC	N412_CD	N412_CSTD
N412_SSA3PTC	N412_CDSS	N412_CSSSTD
	N412_CDSSA	

SINGLE DOOR FREESTANDING	DOUBLE DOOR FREESTANDING
WRD_FS4	WRD_FSD4

CONTINUOUS HINGE CLAMP COVER
N4
SSN4
ALN4



# WIEGMANN®

Wiegmann IP66 rated enclosures are intended for use in housing electrical and electronic controls, instruments, components and associated wiring. They are designed for indoor or outdoor use in protecting components from dust, dirt, oil and hose directed water.

Having IP66 rated enclosures allows our products to be shipped globally. This also provides a benefit for domestic customers requiring international specifications.

## NEMA TO IEC – ENCLOSURE RATING CROSS-REFERENCE\*

NEMA TYPE	IP23	IP30	IP32	IP55	IP64	IP65	IP66	IP67
1	•							
2		•						
3					•			
3R			•					
4							•	
4X							•	
6								•
12				•				
13						•		

*\*Note: This cross-reference table is an approximation of NEMA and IEC classifications for reference only. Please consult the appropriate agency's requirements and test qualifications for complete information.*

