



NON-METALLIC/OPERATOR INTERFACE/DISCONNECTS

Numbers in () represent total part numbers available within family

PRODUCT	NON-METALLIC	OPERATOR INTERFACE	LARGE DISCONNECTS
			WAX-U (6), WACPX-U (6), WAXM-U (13), WAXM3EW (6), WMODX (6)
Size Ranges	6 X 6 X 4 to 90 x 72 x 36	17 x 19 x 6 to 22 x 24 x 12	60 x 49 x 12 to 90 x 196 x 18
Key Features	<ul style="list-style-type: none"> • Fiberglass Reinforced Polyester • Excellent chemical and corrosion resistance • Multiple cover configurations • Screw Cover • CH-SC. • CH-QR • HC-Pull Latch • HC-Link Latch 	<ul style="list-style-type: none"> • Completely assembled. • Available in Cableway or Vertica Series Cable = pivot range only Vertica = vertical and pivotal range 	<ul style="list-style-type: none"> • Floor mounted on 15" H legs (2 door) • Free standing (single or double door) • Multi-door (2, 3, 4 or 5 door)
Standard Features	<ul style="list-style-type: none"> • Fiberglass Reinforced Polyester • FIP polyurethane gasket • Stainless steel hardware • Raised brass inserts for mtg • Optional sub panels • Full 180 degree door opening • Optional opaque or clear covers • Optional mtg foot kits • UV resistant • Non-flame propagating • Temperature range: -40F to 250F • Finish: Gray 	<ul style="list-style-type: none"> • Completely assembled HMI's • Seam Welded • Lift off hinge • 1/4 turn latch access • Grab handle • Stud mtd Alum sub panel incl. • Sealed passageways • Components secured by hard pins • Std. preconfigured cutouts for PanelView, PanelView Plus or VersaView • Vertica: counterbalanced • Standard ground studs • Painted: RAL7035 Textured Gray 	<ul style="list-style-type: none"> • 10 gauge • Seam welded • Continuous hinge • 3 pt padlocking vault handles • Lifting eyes • Light mounting channels • Print pocket • ANSI 61 <p>On WAX-U and WACPX-U, customer must order sub panels separately.</p>
Ratings	NEMA, UL/cUL & CSA Type 1, 3, 3S, 12, 13, 4X UL & CSA	NEMA, UL Type 4 (4X also available)	NEMA Type 12 UL & CSA