


**MILD STEEL - NEMA 12 - ANSI 61 POLYESTER POWDER**

Numbers in ( ) represent total part numbers available within family

PRODUCT LINE	JIC SERIES SERIES	N12 WALL-MOUNT SERIES	DISCONNECT WALL-MOUNT SERIES	FLOOR MOUNT SERIES	FREESTANDING SERIES	MULTI-DOOR SERIES
	B (14), BCH (22), BCHS (4), BSC (16), WAGIE (11), JIC (3), TCH (32), BCHL (20) BCHQR (7)	N12 (85), WAWF (12), WAFM (5)	SDN12 (32), SDN12PL (31), ABN12 (11), N412CSTD (8), N412CSSSTD (5)	N12 (21)	WAFS (14), WAFSD (12), WAFSDA (8), WAFSDAD (5)	WAME (6)
<b>Size Ranges</b>	4 x 4 x 3 to 16 x 14 x 10	16 x 12 x 6 to 72 x 30 x 16	20 x 21 x 8 to 60 x 38 x 16	54 x 42 x 8 to 72 x 72 x 24	60 x 24 x 18 to 90 x 72 x 36	86 x 112 x 14 to 86 x 187 x 20
<b>Key Features</b>	<ul style="list-style-type: none"> <li>Variety of cover options .</li> </ul>	<ul style="list-style-type: none"> <li>Rugged workhorse.</li> <li>Single or two door options Clamps (single door)</li> <li>3pt handle (two door)</li> </ul>	<ul style="list-style-type: none"> <li>Disconnects designed to accept most major handle offerings</li> </ul>	<ul style="list-style-type: none"> <li>Large two-door</li> <li>Industrial floor mounts</li> <li>Overlapping doors</li> <li>3pt keylocking handle</li> <li>Single &amp; dual access</li> </ul>	<ul style="list-style-type: none"> <li>Large two-door</li> <li>Industrial freestandings</li> <li>Overlapping doors</li> <li>3pt keylocking handle</li> </ul>	<ul style="list-style-type: none"> <li>Heavy duty multi-door 3, 4 &amp; 5 door options</li> </ul>
<b>Standard Features</b>	<ul style="list-style-type: none"> <li>Single door junction enclosures</li> <li>Lift off cover</li> <li>Continuous hinge</li> <li>Screw cover</li> <li>Quick release</li> <li>Seam welded construction</li> <li>External mtg feet top &amp; bottom</li> <li>Optional sub panels</li> <li>SS hinge pin</li> <li>ANSI 61 polyester powder</li> </ul>	<ul style="list-style-type: none"> <li>Single door (clamps, hasp &amp; staple)</li> <li>Two door (3pt keylocking handle)</li> <li>Continuous hinge</li> <li>SS hinge pin</li> <li>External mtg feet top &amp; bottom</li> <li>FIP gasket</li> <li>Hasp &amp; staple (padlocking)</li> <li>External mtg feet top &amp; bottom</li> <li>Seam welded construction</li> <li>Optional sub panel</li> <li>FIP (single door)</li> <li>Print pocket</li> <li>ANSI 61 polyester powder</li> </ul>	<ul style="list-style-type: none"> <li>Single door</li> <li>Continuous hinge</li> <li>SS hinge pin</li> <li>External mtg feet top &amp; bottom</li> <li>Optional sub panel</li> <li>FIP (single door)</li> <li>Print pocket</li> <li>ANSI 61 polyester powder</li> </ul>	<ul style="list-style-type: none"> <li>3pt keylocking handles</li> <li>Two door-overlapping</li> <li>Seam welded construction</li> <li>12" floor stands</li> <li>Lifting eyes</li> <li>Continuous hinge</li> <li>Print pocket</li> <li>Collar studs for Optional</li> <li>Sub panels</li> <li>ANSI 61 polyester powder</li> </ul>	<ul style="list-style-type: none"> <li>3pt keylocking handles</li> <li>Single and two door access</li> <li>Seam welded construction</li> <li>Lifting eyes</li> <li>Continuous hinge</li> <li>Print pocket</li> <li>Collar studs for Optional</li> <li>Sub panels</li> <li>ANSI 61 polyester powder</li> </ul>	<ul style="list-style-type: none"> <li>3pt padlocking handles</li> <li>Seam welded construction</li> <li>Heavy duty continuous hinges</li> <li>Lifting eyes</li> <li>Light mtg channels</li> <li>Print pocket</li> <li>Sub panels installed</li> <li>ANSI 61 polyester powder</li> </ul>
<b>Ratings</b>	NEMA Type 12, 13 UL & CSA	NEMA Type 12, 13 UL & CSA	NEMA Type 4, 4X, 12, 13 UL & CSA	NEMA Type 12, 13 UL & CSA	NEMA Type 12, 13 UL & CSA	NEMA Type 12, 13 UL & CSA