

20A 125V 3Wire 2Pole White  
Polyester Face Cover GFCI Standard  
**99398111**

POS: 2-7 MIN: 0 MAX: 0



BRY-Blk 15AMP 125V NEMA 5-15R  
Straight Blade Connector  
**0701989**

POS: 1-8 MIN: 0 MAX: 0



BRY-Blk 15AMP 125V NEMA 5-15P  
Straight Blade Plug  
**0701958**

POS: 1-1 MIN: 0 MAX: 0



20A 125V 3Wire 2Pole Ivory  
Polyester Face Cover GFCI Standard  
**99398107**

POS: 2-8 MIN: 0 MAX: 0



BRY-Brown 20AMP 125V NEMA  
5-20R Duplex Receptacle  
**0702387**

POS: 2-1 MIN: 0 MAX: 0



BRY-Blk 15AMP 125V 2P 3W Straight  
Blade Connector  
**0701342**

POS: 1-2 MIN: 0 MAX: 0



BRY-Blk 30AMP 250V NEMA L6-30P  
Locking Plug  
**0701331**

POS: 3-1 MIN: 0 MAX: 0



BRY-Ivory 20AMP 125V NEMA 5-20  
Duplex Receptacle  
**0703913**

POS: 2-2 MIN: 0 MAX: 0



BRY-Blk 20AMP 125V NEMA 5-20P  
Straight Blade Plug  
**0701961**

POS: 1-3 MIN: 0 MAX: 0



BRY-Blk 30AMP 250V NEMA L6-30C  
Locking Connector  
**0701350**

POS: 3-2 MIN: 0 MAX: 0



BRY-Brown 15A 125V 5-15R HD  
Duplex Receptacle  
**0722778**

POS: 2-3 MIN: 0 MAX: 0



BRY-Blk/Wht 20AMP 125V NEMA  
5-20C Straight Blade Connector  
**0701478**

POS: 1-4 MIN: 0 MAX: 0



BRY-Blk 30AMP 250V NEMA L6-30R  
Grounding Receptacle  
**0700813**

POS: 3-3 MIN: 0 MAX: 0



BRY-Ivory 15A 125V 5-15R HD  
Duplex Receptacle  
**0722779**

POS: 2-4 MIN: 0 MAX: 0



BRY-Ylw 15AMP 2P 3W NEMA 5-15P  
Grounding Plug  
**0700343**

POS: 1-5 MIN: 0 MAX: 0



BRY-Blk 20AMP 125V NEMA L5-20P  
Locking Plug  
**0701326**

POS: 3-4 MIN: 0 MAX: 0



BRY-Brown 20AMP 125V NEMA  
5-20R Duplex Receptacle  
**0701987**

POS: 2-5 MIN: 0 MAX: 0



BRY-Ylw 15AMP 125V 2P 3  
Wire-Ground Plug/Connector  
**0700344**

POS: 1-6 MIN: 0 MAX: 0



BRY-Blk 20AMP 125 NEMA L5-20C  
Connector  
**0701345**

POS: 3-5 MIN: 0 MAX: 0



BRY-Ivory 20AMP 125V NEMA 5-20R  
Duplex Receptacle  
**0701983**

POS: 2-6 MIN: 0 MAX: 0



BRY-Black 15AMP 125V NEMA 5-15P  
Grounding Plug  
**0701988**

POS: 1-7 MIN: 0 MAX: 0



**.73-.97" 1" Steel Lock Nut Bus Grip  
Strain Relief**  
**0703806**

POS: 5-4 MIN: 0 MAX: 0



**.37-.50" 1/2" Male Thread Strain  
Relief Deluxe Cord Grip**  
**0703807**

POS: 5-5 MIN: 0 MAX: 0



**.50-.62" 1/2" Male Thread Strain  
Relief Deluxe Cord Grip**  
**0703808**

POS: 5-6 MIN: 0 MAX: 0



**.50-.62" 3/4" Male Thread Strain  
Relief - Deluxe Cord Grip**  
**0704251**

POS: 5-7 MIN: 0 MAX: 0



**.62-.75" 3/4" Male Thread Strain  
Relief Deluxe Cord Grip**  
**0703809**

POS: 5-8 MIN: 0 MAX: 0



**BRY-Bik 15AMP 250V NEMA L6-15C  
Straight Blade Connector**  
**0701343**

POS: 4-5 MIN: 0 MAX: 0



**.43-.56" Single U Eye Galvanized  
Steel Bus Drop**  
**0703812**

POS: 4-6 MIN: 0 MAX: 0



**.56-.73" Single U Eye Galvanized  
Steel Bus Drop**  
**0703813**

POS: 4-7 MIN: 0 MAX: 0



**.73-.85" Single U Eye Galvanized  
Steel Bus Drop**  
**0703814**

POS: 4-8 MIN: 0 MAX: 0



**.32-.43" 1/2" Stl Lock Nut&Thrd  
Fitting Buss Drop StrnRelief**  
**0703803**

POS: 5-1 MIN: 0 MAX: 0



**.43-.54" 1/2" Steel Lock Nut Bus Drop  
Strain Relief**  
**0703804**

POS: 5-2 MIN: 0 MAX: 0



**.54-.73" 3/4" Steel Lock nut Bus Drop  
Strain Relief**  
**0703805**

POS: 5-3 MIN: 0 MAX: 0



**BRY-Bik 20AMP 125V NEMA L5-20R  
Grounding Receptacle**  
**0700807**

POS: 3-6 MIN: 0 MAX: 0



**BRY-Bik 15AMP 125V NEMA L5-15P  
Locking Plug**  
**0701323**

POS: 3-7 MIN: 0 MAX: 0



**15A 125V L5-15R Black & White  
Locking Connector**  
**0701477**

POS: 3-8 MIN: 0 MAX: 0



**BRY-Bik 20AMP 250V NEMA L6-20P  
Locking Plug**  
**0701327**

POS: 4-1 MIN: 0 MAX: 0



**BRY-Bik 20AMP 250 NEMA L6-20C  
Connector**  
**0701346**

POS: 4-2 MIN: 0 MAX: 0



**BRY-Bik/Wht 20AMP 250V NEMA  
L6-20R Grounding Receptacle**  
**0700808**

POS: 4-3 MIN: 0 MAX: 0



**BRY-Bik 15AMP 250V NEMA L6-15P  
Locking Plug**  
**0701324**

POS: 4-4 MIN: 0 MAX: 0

