

1/2" Powder Coat Aluminum C Type  
Conduit Body  
**0728613**

POS: 2-7 MIN: 0 MAX: 0



6-5/8"Lx2-29/32"Hx1" LB-Type O-Ser  
Alum Conduit w/Cvr-Gasket  
**0722478**

POS: 2-8 MIN: 0 MAX: 0



1" Steel Uninsulated Throat Set  
Screw Connector  
**0700147**

POS: 3-1 MIN: 0 MAX: 0



1" Die Cast Zinc Uninsulated Throat  
Set Screw Connector  
**0700102**

POS: 3-2 MIN: 0 MAX: 0



1-1/2" Die Cast Zinc Insulated Throat  
Set Screw Connector  
**0703612**

POS: 3-3 MIN: 0 MAX: 0



3/4" Straight Uninsulated Liquidtight  
Conduit Connector  
**0722558**

POS: 3-4 MIN: 0 MAX: 0



1-1/4" 90 Degree Uninsulated  
Liquidtight Conduit Connector  
**0701289**

POS: 3-5 MIN: 0 MAX: 0



5-3/4"Lx2-1/2"Hx3/4" LB-Type O-Ser  
Alum Conduit w/Cvr-Gasket  
**0722477**

POS: 1-8 MIN: 0 MAX: 0



3/4" Steel Uninsulated Throat Set  
Screw Connector  
**0722536**

POS: 2-1 MIN: 0 MAX: 0



3/4" Die Cast Zinc Uninsulated  
Throat Set Screw Connector  
**0700101**

POS: 2-2 MIN: 0 MAX: 0



1-1/4" Die Cast Zinc Insulated Throat  
Set Screw Connector  
**0703611**

POS: 2-3 MIN: 0 MAX: 0



1/2" Straight Uninsulated Liquidtight  
Conduit Connector  
**0722557**

POS: 2-4 MIN: 0 MAX: 0



1-1/2" Straight Uninsulated  
Liquidtight Conduit Connector  
**0701276**

POS: 2-5 MIN: 0 MAX: 0



1/2" Malleable Iron 45 Degree  
Uninsulated Conduit Connector  
**0701279**

POS: 2-6 MIN: 0 MAX: 0



1/2" Steel Uninsulated Throat Set  
Screw Connector  
**0722535**

POS: 1-1 MIN: 0 MAX: 0



1/2" Die Cast Zinc Uninsulated  
Throat Set Screw Connector  
**0700100**

POS: 1-2 MIN: 0 MAX: 0



1" Die Cast Zinc Insulated Throat Set  
Screw Connector  
**0703610**

POS: 1-3 MIN: 0 MAX: 0



3/8" Straight Uninsulated Liquidtight  
Conduit Connector  
**0722556**

POS: 1-4 MIN: 0 MAX: 0



1-1/4" Straight Uninsulated  
Liquidtight Conduit Connector  
**0701275**

POS: 1-5 MIN: 0 MAX: 0



3/8" Malleable Iron 45 Degree  
Uninsulated Conduit Connector  
**0701278**

POS: 1-6 MIN: 0 MAX: 0



5-3/32"Lx2-9/32"Hx1/2" LB-Type  
O-Ser Alum Cond w/Cvr-Gasket  
**0722476**

POS: 1-7 MIN: 0 MAX: 0



Image Not Available

Image Not Available



3/4" Die Cast Zinc Coupling

**0700161**

POS: 5-4 MIN: 0 MAX: 0



2" Straight Uninsulated Liquidtight Conduit Connector

**0703649**

POS: 5-5 MIN: 0 MAX: 0



1-1/4" Malleable Iron 45Degree Uninsulated Conduit Connector

**0701282**

POS: 5-6 MIN: 0 MAX: 0



1-1/4" Powder Coat Aluminum C Type Conduit Body

**0728616**

POS: 5-7 MIN: 0 MAX: 0



5-3/8"Lx1-5/8"Hx3/4" LL-Type O-Ser Alum Conduit w/Cvr-Gasket

**0722484**

POS: 5-8 MIN: 0 MAX: 0



Image Not Available

2" Steel Uninsulated Throat Set Screw Connector

**0700150**

POS: 6-1 MIN: 0 MAX: 0



2" Die Cast Zinc Uninsulated Throat Set Screw Connector

**0700105**

POS: 6-2 MIN: 0 MAX: 0



1-1/2" 90 Degree Uninsulated Liquidtight Conduit Connector

**0701290**

POS: 4-5 MIN: 0 MAX: 0



1" Malleable Iron 45 Degree Uninsulated Conduit Connector

**0701281**

POS: 4-6 MIN: 0 MAX: 0



1" Powder Coat Aluminum C Type Conduit Body

**0728615**

POS: 4-7 MIN: 0 MAX: 0



4-5/8"Lx1-5/8"Hx1/2" LL-Type O-Ser Alum Conduit w/Cvr-Gasket

**0722483**

POS: 4-8 MIN: 0 MAX: 0



1-1/2" Steel Uninsulated Throat Set Screw Connector

**0700149**

POS: 5-1 MIN: 0 MAX: 0



1-1/2" Die Cast Zinc Uninsulated Throat Set Screw Connector

**0700104**

POS: 5-2 MIN: 0 MAX: 0



1" Trade Size EMT Steel Coupling

**0700207**

POS: 5-3 MIN: 0 MAX: 0



3/4" Malleable Iron 45 Degree Uninsulated Conduit Connector

**0701280**

POS: 3-6 MIN: 0 MAX: 0



3/4" Powder Coat Aluminum C Type Conduit Body

**0728614**

POS: 3-7 MIN: 0 MAX: 0



7-1/2"Lx3-3/16"Hx1-1/4" LB-Type O-Ser AlumCond w/Cvr-Gasket

**0722479**

POS: 3-8 MIN: 0 MAX: 0



Image Not Available

1-1/4" Steel Uninsulated Throat Set Screw Connector

**0700148**

POS: 4-1 MIN: 0 MAX: 0



1-1/4" Die Cast Zinc Uninsulated Throat Set Screw Connector

**0700103**

POS: 4-2 MIN: 0 MAX: 0



2" Die Cast Zinc Insulated Throat Set Screw Connector

**0703613**

POS: 4-3 MIN: 0 MAX: 0



1/2" Die Cast Zinc Coupling

**0700160**

POS: 4-4 MIN: 0 MAX: 0



3/4" Steel Insulated Throat Set Screw Connector  
**0703585**  
POS: 8-1 MIN: 0 MAX: 0



2" Steel Insulated Throat Set Screw Connector  
**0703589**  
POS: 8-2 MIN: 0 MAX: 0



1/2" Trade Size EMT Steel Coupling  
**0722537**  
POS: 8-3 MIN: 0 MAX: 0



1-1/2" Die Cast Zinc Coupling  
**0700164**  
POS: 8-4 MIN: 0 MAX: 0



3/4" 90Deg Uninsulated Liquidtight Conduit Connector  
**0722561**  
POS: 8-5 MIN: 0 MAX: 0



1/2" O-Series Neoprene Gasket  
**0703843**  
POS: 8-6 MIN: 0 MAX: 0



1" Fiber Conduit Body Gasket  
**0728609**  
POS: 8-7 MIN: 0 MAX: 0



1-1/2" Steel Insulated Throat Set Screw Connector  
**0703588**  
POS: 7-2 MIN: 0 MAX: 0



1-1/2" Trade Size EMT Steel Coupling  
**0700209**  
POS: 7-3 MIN: 0 MAX: 0



1-1/4" Die Cast Zinc Coupling  
**0700163**  
POS: 7-4 MIN: 0 MAX: 0



1/2" 90Deg Uninsulated Liquidtight Conduit Connector  
**0722560**  
POS: 7-5 MIN: 0 MAX: 0



2" Malleable Iron 45 Degree Uninsulated Conduit Connector  
**0701284**  
POS: 7-6 MIN: 0 MAX: 0



3/4" Fiber Conduit Body Gasket  
**0728608**  
POS: 7-7 MIN: 0 MAX: 0



4-5/8" Lx1-3/8" Hx1/2" LR-Type O-Ser Alum Conduit w/Cvr-Gasket  
**0722486**  
POS: 7-8 MIN: 0 MAX: 0



1-1/4" Trade Size EMT Steel Coupling  
**0700208**  
POS: 6-3 MIN: 0 MAX: 0



1" Die Cast Zinc Coupling  
**0700162**  
POS: 6-4 MIN: 0 MAX: 0



3/8" 90Deg Uninsulated Liquidtight Conduit Connector  
**0722559**  
POS: 6-5 MIN: 0 MAX: 0



1-1/2" Malleable Iron 45Degree Uninsulated Conduit Connector  
**0701283**  
POS: 6-6 MIN: 0 MAX: 0



1/2" Fiber Conduit Body Gasket  
**0728607**  
POS: 6-7 MIN: 0 MAX: 0



6-1/4" Lx2" Hx1" LL-Type O-Ser Alum Conduit w/Cvr-Gasket  
**0722485**  
POS: 6-8 MIN: 0 MAX: 0

Image Not Available

1/2" Steel Insulated Throat Set Screw Connector  
**0703584**  
POS: 7-1 MIN: 0 MAX: 0



1-1/4"-1-1/2" Plant Fiber Conduit  
Body Gasket

**0728610**

POS: 9-7 MIN: 0 MAX: 0



Image Not Available

5-3/8"Lx1-5/8"Hx3/4" LR-Type O-Ser  
Alum Conduit w/Cvr-Gasket

**0722487**

POS: 8-8 MIN: 0 MAX: 0



6-1/4"Lx2"Hx1" LR-Type O-Ser Alum  
Conduit w/Cvr-Gasket

**0722488**

POS: 9-8 MIN: 0 MAX: 0



Image Not Available

1" Steel Insulated Throat Set Screw  
Connector

**0703586**

POS: 9-1 MIN: 0 MAX: 0



1/2" Die Cast Zinc Insulated Throat  
Set Screw Connector

**0703608**

POS: 9-2 MIN: 0 MAX: 0



3/4" Trade Size EMT Steel Coupling

**0722538**

POS: 9-3 MIN: 0 MAX: 0



2" Die Cast Zinc Coupling

**0700165**

POS: 9-4 MIN: 0 MAX: 0



1" 90Deg Uninsulated Liquidtight  
Conduit Connector

**0722562**

POS: 9-5 MIN: 0 MAX: 0



3/4" O-Series Neoprene Gasket

**0703844**

POS: 9-6 MIN: 0 MAX: 0

