

20A 125V 5-20R Ivory Heavy Duty
Spec Grade Duplex Recept
0736177
POS: 2-7 MIN: 0 MAX: 0

20A 125V 5-20R White Heavy Duty
Industrial Grade Duplex Receptacle
0736185
POS: 2-8 MIN: 0 MAX: 0

20A 125V 5-20R Brown Hubbell-Pro
Indus. Grade Duplex Recept
0731932
POS: 3-1 MIN: 0 MAX: 0

20A 125V 5-20R Ivory Hubbell-Pro
Indus. Grade Duplex Recept
0731939
POS: 3-2 MIN: 0 MAX: 0

20A 125V 5-20R SM White Industrial
Grade Duplex Straight Blade
0731945
POS: 3-3 MIN: 0 MAX: 0

20A 125V 5-20R Brown Comm Spec
Grade Duplex Receptacles
0732345
POS: 3-4 MIN: 0 MAX: 0

20A 125V5-20R Ivory C-Grade
SelectSpec Duplex Receptacles
0732358
POS: 3-5 MIN: 0 MAX: 0



15A 125V 5-15R Ylw Valise
Connector Body
0736388
POS: 1-8 MIN: 0 MAX: 0

15A 125V 5-15P ELASTOGRIP[REG]
Series Straight Blade Standard Plug
0734401
POS: 2-1 MIN: 0 MAX: 0

15A 125V 5-15R Yellow
ELASTOGRIP[REG] Series Straight
0734406
POS: 2-2 MIN: 0 MAX: 0

15A/125V NEMA 5-15 Yellow
Watertight Straight Blade Plug
0747822
POS: 2-3 MIN: 0 MAX: 0

15A/125V NEMA 5-15 Yellow
Watertight Straight Blade Connector
0747827
POS: 2-4 MIN: 0 MAX: 0

20A 125V 5-20R Brown Heavy Duty
Spec Grade Duplex Recept
0736169
POS: 2-5 MIN: 0 MAX: 0

20A 125V 5-20R Gray Heavy Duty
Spec Grade Duplex Receptacle
0736174
POS: 2-6 MIN: 0 MAX: 0



15A 125V 5-15 Black INSULGRIP
Straight Blade Plug
0736082
POS: 1-1 MIN: 0 MAX: 0

15A 125V 5-15 Black/White
INSULGRIP[REG] Hospital Grade
0736083
POS: 1-2 MIN: 0 MAX: 0

15A 125V 5-15 Black/White
INSULGRIP Series Connector Body
0736086
POS: 1-3 MIN: 0 MAX: 0

20A 125V 5-20 Black INSULGRIP
Straight Blade Plug
0736193
POS: 1-4 MIN: 0 MAX: 0

20A 125V 5-20 Black/White Insulgrip
Series Connector Body
0736195
POS: 1-5 MIN: 0 MAX: 0

20A 250V 6-20 Black INSULGRIP
Straight Blade Plug
0736218
POS: 1-6 MIN: 0 MAX: 0

15A 125V 5-15P Yellow INSULGRIP
Valise Plug
0736380
POS: 1-7 MIN: 0 MAX: 0



20A 250V L6-20R Black/Wht
TWIST-LOCK Conn Body
0734743
POS: 5-7 MIN: 0 MAX: 0



15A 125V L5-15P Black/White
TWIST-LOCK Plug
0735803
POS: 4-8 MIN: 0 MAX: 0



20A 125V 5-20R B/S White
Commercial Grade Duplex Straight
0732368
POS: 3-6 MIN: 0 MAX: 0



20A 250V L6-20R Black TWIST-LOCK
Receptacle
0734729
POS: 5-8 MIN: 0 MAX: 0



15A 250V L6-15P Black/Wht
TWIST-LOCK Plug
0735689
POS: 5-1 MIN: 0 MAX: 0



20A 125V 5-20R Brown Commercial
Series Duplex Receptacle
0732697
POS: 3-7 MIN: 0 MAX: 0



1/2" Aluminum .19"-.25" Straight
Male Cord Connector
0744768
POS: 6-1 MIN: 0 MAX: 0



15A 125V L5-15R Black/White
TWIST-LOCK Connector Body
0735809
POS: 5-2 MIN: 0 MAX: 0



20A 125V 5-20R Ivory Commercial
Series Duplex Receptacle
0732716
POS: 3-8 MIN: 0 MAX: 0



1/2" Aluminum .31"-.38" Straight
Male Cord Connector
0744770
POS: 6-2 MIN: 0 MAX: 0



20A 125V L5-20P Black/Wht
TWIST-LOCK Plug
0734713
POS: 5-3 MIN: 0 MAX: 0



20A 125V 5-20R White Commercial
Grade Duplex Receptacle
0732734
POS: 4-1 MIN: 0 MAX: 0



1/2" Aluminum .38"-.44" Straight
Male Cord Connector
0744771
POS: 6-3 MIN: 0 MAX: 0



20A 125V L5-20R Black/Wht
TWIST-LOCK Conn Body
0734720
POS: 5-4 MIN: 0 MAX: 0



30A 250V L6-30P Black/Wht
TWIST-LOCK Plug
0734995
POS: 4-5 MIN: 0 MAX: 0



1/2" Aluminum .19"-.25" Straight
Male Cord Connector
0744778
POS: 6-4 MIN: 0 MAX: 0



20A 125V L5-20R Black TWIST-LOCK
Receptacle
0734707
POS: 5-5 MIN: 0 MAX: 0



30A 250V L6-30R Black/Wht
TWIST-LOCK Conn Body
0735003
POS: 4-6 MIN: 0 MAX: 0



1/2" Aluminum .25"-.38" Straight
Male Cord Connector
0744782
POS: 6-5 MIN: 0 MAX: 0



20A 250V L6-20P Black/Wht
TWIST-LOCK Plug
0734736
POS: 5-6 MIN: 0 MAX: 0



30A 250V L6-30R Black TWIST-LOCK
Receptacle
0734989
POS: 4-7 MIN: 0 MAX: 0



3/4" NPT .62"-.75" Straight Male Deluxe Strain Relief Cord Grip
0731393
POS: 8-4 MIN: 0 MAX: 0



1/2" Gray Nylon Straight Male Liquid Tight Connector
0741790
POS: 7-5 MIN: 0 MAX: 0



1/2" Aluminum .38"-.50" Straight Male Cord Connector
0744786
POS: 6-6 MIN: 0 MAX: 0



1/2" NPT .37"-.50" 90-Degree Male Strain Relief Deluxe Cord Grip
0731419
POS: 8-5 MIN: 0 MAX: 0



3/4" Gray Nylon Straight Male Liquid Tight Connector
0741794
POS: 7-6 MIN: 0 MAX: 0



1/2" Aluminum .50"-.63" Straight Male Cord Connector
0744790
POS: 6-7 MIN: 0 MAX: 0



.43"-.56"x10.75" Galv Steel KELLEMS Single Eye Bus Drop Wide
0731364
POS: 8-6 MIN: 0 MAX: 0



1/2" Gray Nylon Swivel Male Liquid Tight Connector
0742682
POS: 7-7 MIN: 0 MAX: 0



1/2" Aluminum .625"-.750" Straight Male Cord Connector
0744796
POS: 6-8 MIN: 0 MAX: 0



.56"-.73"x13" Galv Steel KELLEMS Single Eye Bus Drop Wide Range
0731365
POS: 8-7 MIN: 0 MAX: 0



3/4" Gray Nylon Swivel Male Liquid Tight Connector
0742685
POS: 7-8 MIN: 0 MAX: 0



3/4" Aluminum .38"-.50" Straight Male Cord Connector
0744807
POS: 7-1 MIN: 0 MAX: 0



.73"-.85"x13.75" Galv Steel KELLEMS Single Eye Bus Drop Wide
0731366
POS: 8-8 MIN: 0 MAX: 0



1/2" NPT .37"-.50" Straight Male Deluxe Strain Relief Cord Grip
0731387
POS: 8-1 MIN: 0 MAX: 0



3/4" Aluminum .50"-.63" Straight Male Cord Connector
0744809
POS: 7-2 MIN: 0 MAX: 0



1/2" NPT .43"-.54" Non-Insulated Strain Relief Dust Tight Cord Grip
0731348
POS: 9-1 MIN: 0 MAX: 0



1/2" NPT .50"-.62" Straight Male Deluxe Strain Relief Cord Grip
0731388
POS: 8-2 MIN: 0 MAX: 0



3/4" Aluminum .50"-.63" Straight Male Cord Connector
0744814
POS: 7-3 MIN: 0 MAX: 0



3/4" NPT .54"-.73" Non-Insulated Strain Relief Dust Tight Cord Grip
0731349
POS: 9-2 MIN: 0 MAX: 0



3/4" NPT .50"-.62" Straight Male Deluxe Strain Relief Cord Grip
0731392
POS: 8-3 MIN: 0 MAX: 0



3/4" Aluminum .63"-.75" Straight Male Cord Connector
0744817
POS: 7-4 MIN: 0 MAX: 0



1"NPT .73"-.97" Non-Insulated Strain
Relief Dust Tight Cord Grip
0731350

POS: 9-3 MIN: 0 MAX: 0




1-1/4"NPT .97"-1.2" Non-Insulated
Strain Relief Dust Tight Cord Grip
0731351

POS: 9-4 MIN: 0 MAX: 0




.50"-.62"x17" Tin-Ctd Brnz KELLEMS
Single Eye Closed Mesh Std Duty
0730744

POS: 9-5 MIN: 0 MAX: 0




.75"-.99"x21" Tin-Ctd Brnz KELLEMS
Single Eye Closed Mesh Std Duty
0730746

POS: 9-6 MIN: 0 MAX: 0




1"-1.24"x23" Tin-Ctd Brnz KELLEMS
Single Eye Closed Mesh Std Duty
0730747

POS: 9-7 MIN: 0 MAX: 0




.46"-.56" Bronze Closed Mesh Light
Duty Single Eye Service Drop
0730977

POS: 9-8 MIN: 0 MAX: 0


