Straight Blade Residential Devices

15A, 125V, 2Pole 3 Wire Grounding 20 Amp Branch Circuit Rated

CLAMP **Duplex Receptacle**

Features

- Eliminates the need to loop the wire
- External back-wire clamp for fast and easy installation of 15A & 20A branch circuits in residential applications
- Compression plates maximize holding power to provide a stronger, more secure connection
- Terminate up to 8 wires
- Accommodates #12 & #14 AWG wire
- Break-off tabs for switched receptacle applications
- Tamper-resistant shutter complies with NEC®

Ordering Information			
Description	Device Color	UPC	Catalog Number
Tamper-Resistant,	Ivory	883778308253	RR15SITRX
15A 125V Duplex	Light Almond	883778308246	RR15SLATRX
20A Circuit Rated	White	883778308239	RR15SWTRX

Listings

UL Listed to UL498 File No. E2186 File No. E2186 Certified to CSA C22.2, No. 42 NEMA® WD-6 Compliant

Specifications

Face PVC **PVC** Base

.030 in. (.8) Brass **Power Contacts**

Ground Contacts Brass

Wire Clamp .030 (.8) Brass

#14AWG accommodation

Push Wire #14 AWG accommodation

Plated steel **Terminal Screws** Mounting Strap .040 in. (1) steel

Screw & Self-grounding staple Grounding

Mounting Screws Galvanized Steel

Performance

Electrical

Current Interrupting Certified for current interrupting at full rated current

Dielectric Voltage Withstands 2,000V minimum

Mechanical

Product Identification Ratings are a permanent part of the device

Terminal Accommodation #14-#12 AWG copper stranded or solid conductor only Terminals identified in accordance with UL 498 and CSA Terminal Identification

Environmental

Flammability UL 94 5VA

Operating Temperatures Maximum continuous 75°C; minimum -40°C (w/o impact)

Dimensions in Inches (mm)

Hubbell Wiring Device-Kellems • Hubbell Incorporated (Delaware) • 40 Waterview Drive • Shelton, CT 06484 Phone (800) 288-6000 • Fax (800) 255-1031 • Specifications subject to change without notice.

HUBBELL









