

# BUILDING MOUNT

selection guide



HID/CFL Replacement

Mounting Height

18 Feet and up	 <b>LNC4-44L</b>   <b>TRAVERSE</b> 	 <b>WGH-225L</b>	400w   200w HID
12-15 Feet	 <b>LNC3-24L</b>   <b>SG2</b>   <b>TRP2</b>   <b>RDI2</b>  <b>QSP2</b>	 <b>WGH-110L</b>	200w   100w HID
10-12 Feet	 <b>LNC2-18L</b>  <b>SG1</b>  <b>TRP2 Low Glare</b>  <b>RDI2 Low Glare</b>	 <b>PGM3</b>   <b>PVL3</b>   <b>WGH-110L</b>	100w   70w HID
Up to 10 Feet	 <b>LNC2-12L</b>   <b>LNC2-9L</b>  <b>LNC-9L</b>  <b>LNC2-7L</b>  <b>LNC-7L</b>  <b>LNC-5L</b>	 <b>TRP1</b>   <b>RDI1</b>   <b>GSP1</b>   <b>WGH-81L</b>  <b>NRG-356LU</b>	42w   26w CFL

See reverse side for fixture data

 = Battery Back up

# Building Mount Selection Guide

Luminaire	Spacing	Mounting Height	# LEDs	Delivered Lumens	System Watts	Energy Savings	Equivalency	LPW	CCT	Drivers/ Current	Voltage	DLC Approved	Battery Back up	Photocell	Motion Sensor
LNC4-105	4 X	18 ft and up	36-44	11-14,800	125-170	70%	400w	88	3K/4K/5K	2@1150mA	120-480V	YES	-	Twist lock + button	YES
TRV-48L/60L	4 X	18 ft and up	48-60	12-15,000	110-136	71%	400w	103	3K/4K/5K	1@700mA	120-480V	YES	-	Button	YES
WGH-225L	3 X - 4 X	18 ft and up	225	12,000	97	76%	400w	105	4K/5K	1@125mA	120-277V	YES	-	Button	-
TRP2/RD12/QSP2	4 X	15 - 20 ft	24-32	3,700-10,800	28-83	77%	150w/400w	146	3K/4K/5K	350mA-1100mA	120-277V	YES	YES	Button	YES
TRP2/RD12 Low Glare	4 X	15 - 20 ft	180	3,000-9,000	28-62	76%	100w/250w	145	3K/4K/5K	100mA-150mA	120-277V	YES	-	Button	YES
SG2-50/SG2-80	3 X - 4 X	15 - 20 ft	3	5500/8000	50/80	72%	175w/250w	101/110	4K/5K	415mA/650mA	120-277V	YES	YES	Button	YES
LNC4-065	4 X	15 - 20 ft	36-44	7-9,500	80-100	72%	250w	95	3K/4K/5K	2@650mA	120-480V	YES	YES	Twist lock + button	YES
TRV-24L/36L	4 X	15 - 20 ft	24-36	6-9,000	55-90	72%	250w	103	3K/4K/5K	1@700mA	120-480V	YES	36L only	Button	YES
PGM3/PVL3	3 X - 4 X	12 - 15 ft +	180	7,160/5,978	72	72%	250w	99.4/83	3K/4K/5K	2@700mA	120-277V, 347V	YES	YES	Button	YES
LNC3-24L-105	4 X	15 - 20 ft	24	7,500	83	71%	250w	92	3K/4K/5K	1@1050mA	120-277V, 347V*/480V	-	YES	Twist lock + button	YES
LNC3-24L-075	4 X	12 - 18 ft	24	5,900	60	74%	200w	99	3K/4K/5K	1@750mA	120-277V	YES	YES	Twist lock + button	YES
WGH-110L	3 X - 4 X	12 - 15 ft +	110	6,400	53	78%	250w	92	3K/4K/5K	1@140mA	120-277V	YES	-	Button	-
LNC3-24L-050	4 X	12 - 18 ft	24	4,100	60	80%	175w	101	3K/4K/5K	1@500mA	120-277V	YES	YES	Twist lock + button	YES
LNC2-18L	4 X	10 - 15 ft	18	4,100	42.7	72%	150w	97	3K/4K/5K	1@700mA	120-277V	YES	-	Button	YES
PGM3/PVL3-035	3 X - 4 X	10 - 15 ft	180	3,300	14	83%	150w	105	4K/5K	1@115mA	120-277V	YES	-	Button	-
WGH-81L	3 X - 4 X	Up to 12 ft	81	3,300	14	83%	150w	150	4K/5K	1@115mA	120-277V	YES	-	Button	-
SG1-20/SG1-30	3 X - 4 X	10 - 15 ft	2	2200/3200	20/30	72%	150w	106/110	4K/5K	250mA/350mA	120-277V	YES	-	Button	-
TRP1/RD11/QSP1-030	4 X	10 - 15 ft	12	2,900	28	84%	150w	104	3K/4K/5K	1@700mA	120-277V	YES	YES	Button	YES
LNC2-12L	4X	12 - 15 ft	12	2,900	28	80%	150w	102	3K/4K/5K	1@700mA	120-277V	YES	YES	Button	YES
TRP1/RD11/QSP1-020	4 X	Up to 12 ft	12	2,300	20	84%	100w	114	3K/4K/5K	1@500mA	120-277V	YES	YES	Button	YES
LNC2-9L/LNC-9L	4 X	10 - 12 ft +	9	2,100	17	78%	100w	95	3K/4K/5K	1@700mA	120-277V	YES	-	Button	YES
TRP1/RD11/QSP1-015	4 X	Up to 12 ft	12	1,600	14	84%	70w	118	3K/4K/5K	1@350mA	120-277V	YES	YES	Button	YES
LNC2-7L/LNC-7L	4 X	Up to 11 ft	7	1,600	17	77%	70w	91	3K/4K/5K	1@700mA	120-277V	YES	-	Button	YES
NRG-356LU	1X - 2X	Up to 10 ft	56	1,200	18	75%	70w	100	5000K	1@350mA	120-277V	YES	-	Button	YES
LNC-5L	4 X	Up to 10 ft	5	1,100	13	74%	50w	88	3K/4K/5K	1@700mA	120-277V	YES	-	Button	-