

BUILDING MOUNT

selection guide



HID/CFL Replacement








Mounting Height

18 Feet and up	LNC4-44L* TRAVERSE	WGH-225L*	400w 200w HID
12-15 Feet	LNC3-24L* LMC-30L TRP-30L RDI-30L QSP-30L DDL-140L-1* DDL-9L1/DDL-56L* PGM3* PVL3*	WGH-110L*	200w 100w HID
10-12 Feet	LNC2-18L* LNC2-12L* LNC2-9L* LNC-9L*		100w 70w HID
Up to 10 Feet	LNC2-7L* LNC-7L* LNC-5L* ALFW-6LU* EUROLUXE* NRG-356LU* VWGL-1*		42w 26w CFL

See reverse side for fixture data

*EXPRESSLINE = Battery Back up

Building Mount Selection Guide

	Luminaire	Spacing	Mounting Height	# LEDs	Delivered Lumens	System Watts	Energy Savings	Equivalency	LPW	CCT	Drivers/ Current	Voltage	DLC Approved	Battery Back up	Photocell	Motion Sensor
	LNC4-105	4 X	18 ft and up	36-44	10-15,000	125-170	70%	400w	88	4000K	2@1150mA	120-480V	YES	-	Twist lock	YES
	Traverse	4 X	18 ft and up	48-60	12-15,000	110-136	71%	400w	103	5000K	1@700mA	120-480V	YES	-	Button	YES
	WGH-225L*	3 X - 4 X	18 ft and up	225	10,151	97	76%	400w	105	4000K	1@125mA	120-277V	YES	-	Button	-
	LNC4-065	4 X	18 ft and up	36-44	7,500/9,500	80-100	92%	250w	95	4000K	2@650mA	120-480V	YES	YES	Twist lock	YES
	Traverse	4 X	15 - 20 ft	24-36	6,000/9,000	55-90	72%	250w	103	5000K	1@700mA	120-480V	YES	36L only	Button	YES
	PGM3/PVL3*	3 X - 4 X	12 - 15 ft +	180	7,160/5,978	72	72%	250w	99.4/83	5000K	2@700mA	120-277V, 347V*	YES	YES	Button	YES
	LNC3-24L	4 X	15 - 20 ft	24	4,104/ 7,559	41/60/83	71%	250w	up to 100	3K/4K/5K	1@500 or 700mA	120-277V, 347V*	YES	YES	Twist lock	YES
	Laredo LMC-30L	4 X	12 - 15 ft +	30	6,023	71.7	71%	250w	84	5000K	2@700mA	120-277V, 347V*	YES	-	Button	YES
	DDL-140L-1*	4 X	12 - 15 ft +	140	5,279	43.5	71%	250w	121	5000K	1@92mA	120V	YES	-	Twist-Lock	-
	Spaulding TRP/RDI/QSP	4 X	12 - 15 ft +	30	5,062	53	74%	200w	96	5000K	1@525mA	120-277V	YES	-	Button	YES
	WGH-110L*	3 X - 4 X	12 - 15 ft	110	4,888	53	78%	250w	92	4000K	1@140mA	120-277V	YES	-	Button	-
	Spaulding TRP/RDI/QSP	4 X	12 - 15 ft	30	3,583	34	77%	150w	105	5000K	1@350mA	120-277V	YES	TRP only	Button	YES
	Laredo LMC-30L-035	4 X	12 - 15 ft	30	3,448	35.4	76%	150w	97.4	5000K	1@350mA	120-277V, 347V*	YES	YES	Button	YES
	DDL-9L1*	4 X	12 - 15 ft	9	3,900	39.5	77%	175w	99	5000K	1@1280mA	120V	YES	-	Twist-Lock	-
	LNC2-18L*	4 X	12 - 15 ft	18	3,122-4,166	42.7	72%	150w	73-97.5	3K/4K/5K	2@700mA	120-277V	YES	-	Button	YES
	DDL-56L*	4 X	12 - 15 ft	56	2,906	30	78%	175w	97	4000K	1@150mA	120V	YES	-	Twist-Lock	-
	LNC2-12L*	4X	12 - 15 ft	12	2,047-2,869	28	80%	150w	73-102.5	3K/4K/5K	1@700mA	120-277V	YES	YES	Button	YES
	LNC2-9L/LNC-9L*	4 X	10 - 12 ft	9	1,588-2,895	17	78%	100w	72-95	3K/4K/5K	1@700mA	120-277V	YES	-	Button	YES
	LNC2-7L/LNC-7L*	4 X	Up to 11 ft	7	1,272-1,557	17	77%	70w	75-91.5	3K/4K/5K	1@700mA	120-277V	YES	-	Button	YES
	NRG-356LU*	1X - 2X	Up to 10 ft	12	1,204	18	64%	50w	67	5000K	1@350mA	120-277V	YES	-	Button	YES
	LNC-5L*	4 X	Up to 10 ft	5	849-1,150	13	74%	50w	65-88.5	3K/4K/5K	1@700mA	120-277V	YES	-	Button	-
	ALFW-6LU-5KBZPC*	3 X	Up to 10 ft	6	905	10.1	85%	70w	90	5000K	1@470mA	120-277V	Not Applicable	-	-	YES
	Eurolux*	3 X	Up to 10 ft	6	830	15	64%	42w CFL	55	5000K	1@700mA	120-277V	Not Applicable	-	-	-
	VWGL-1*	1X - 2X	Up to 10 ft	1	757	11	92%	150w	70	4100K	1@250mA	120-277V	Not Applicable	-	-	-