## HUBBELL<sup>®</sup> Power Systems, Inc.

1850 Richland Ave East Aiken, SC 29801 Phone: 803-648-8386 www.Hubbell.com

# 25/28 kV ELBOW TAP PLUG

Conforms to all Requirements of IEEE Std. 386 - Latest Revision

#### Ratings

Maximum Continuous Voltage...... 16.2 kV Phase-to-Ground Continuous Current.......600 A

#### **Short-Time Current Ratings**

0.17 Sec. Duration......25,000 A rms Symmetrical 3.00 Sec. Duration......10,000 A rms Symmetrical

#### **Insulation Withstand Voltages**


#### **Overload Current**

4 Hour Rating ......900 A

#### **Production Tests**

100% factory tested for Partial Discharge and either AC 60 Hz (60 Hz for 60 Sec.) or Impulse (BIL) (125 kV 1.2 x 50  $\mu$ Sec. wave) Test Point Verification Performed.





### NOTES:

- 1. DIM: IN(MM)
- 2. HEX-BROACH FOR TORQUE IN INSTALLATION INCLUDED.

