


TABLE	
CATALOG NO.	L
B2G10G69SV	10.00 [254]
B2G11G69SV	11.00 [279]
B2G12G69SV	12.00 [305]

REV.	DATE	DESCRIPTION	ECO	BY	C'K'D.
A	3/19/02	DRAWING RELEASED	7456	PL	JLM



NOTES:

- APPROXIMATE AMP RATING: INDOOR = 700, OUTDOOR = 840. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.
- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.

TO ORDER BURNDY PRODUCTS CALL 1-800-346-4175
 MANCHESTER, NH 03109, USA
 FOR PRODUCT INFO = <http://www.fciconnect.com>

BRAID, FLEXIBLE

CAT NO: B2G--G69SV (TABLE)	SCALE 1:1
DRAWN: P LAPONIUS 3/19/02	CHECKED: J MICHAUD 3/19/02
DSGN APPVL: J MICHAUD 3/14/02	MFG APPVL: N/A
Q.A. APPVL: J BRODEUR 3/15/02	
MKTG APPVL: D HAMILTON 3/15/02	
CAD FILE: 10003409-01_A	
MDL REF: N/A	
DRAWING NO. 10003409	REV A
SHEET 1 OF 1	

FCI