


REV.	DATE	DESCRIPTION	ECO	BY	C'K'D.
B	12/10/07	ADD NOTE 5 WITH FLAG.	15258	RB	PL



NOTES:

- MATERIAL: FERRULES - COPPER  
BRAID - TINNED COPPER
- FINISHED: UNPLATED
- APPROXIMATE AMP RATING: INDOOR = 960, OUTDOOR = 1150. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.
- DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.

[5] 'UL' SYMBOL PER INTERNAL SPEC. L4219, LOCATION AND SIZE TO BE DETERMINED BY MANUFACTURING.

TO ORDER BURNDY PRODUCTS CALL 1-800-346-4175  
MANCHESTER, NH 03109, USA  
FOR PRODUCT INFO = <http://www.fciconnect.com>

FLEXIBLE BRAID

ITEM NO: 10008972

CAT NO: B3G18NSL

SCALE: 1/1	
DRAWN BY: R.BOISVERT	6/24/02
CHECKER: J.MICHAUD	6/25/02
DSN APPVL: J.MICHAUD	6/19/02
MFG APPVL: N/A	--
QC APPVL: J.BRODEUR	6/20/02
MKT APPVL: D.HAMILTON	6/19/02
PROD FAM: --	
PROJECT #: --	SIZE
DOCUMENT TYPE: Sales	D
REL LEVEL: AUTOCAD	

DRAWING NO	REV
10009620	B
SHEET 1 OF 1	

**BURNDY PRODUCTS**