



| REV. | DATE | DESCRIPTION | ECO | BY | C'K'D. |
|------|---------|------------------|------|----|--------|
| A | 2/21/03 | DRAWING RELEASED | 8328 | PL | DB |

NOTES:

1. MATERIAL: FERRULES - COPPER
BRAID - TINNED COPPER
2. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
3. APPROXIMATE AMP RATING: INDOOR = 340, OUTDOOR = 405.
THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.

TO ORDER BURNDY PRODUCTS CALL 1-800-346-4175
MANCHESTER, NH 03109, USA
FOR PRODUCT INFO [REDACTED]

FLEXIBLE BRAID

ITEM NO: 33216E

CAT NO: BE24G113

| | | |
|---------------|---------------|---------------|
| DATE: 1/1 | DATE: 2/21/03 | BURNDY |
| DATE: 2/21/03 | DATE: 2/21/03 | |
| DATE: 2/21/03 | DATE: 2/21/03 | |
| DATE: 2/21/03 | DATE: 2/21/03 | |

DRAWING NO: 10023092

SHEET 1 of 1