


BOEING CD. SPEC. 416-0917-()	CATALOG NUMBER	WIRE SIZE (STR AWG)	STUD SIZE	COLOR STRIPES	'C' DIA.		'K' DIA.		L MAX.	M	T		Y MAX.	Z MIN.	WIRE SIZE (STR AWG)	MR10G6 FULL CYCLE HAND RATCHET TOOL
					MAX.	MIN.	MAX.	MIN.			MAX.	MIN.				
-002	YAES18K-1NK	22-18	#6	RED	.230	.222	.152	.142	.755	.090	.035	.029	.644	.202	7/32	RED GRDDVE
-003	YAES18K-49NK	22-18	#8	RED	.318	.306	.178	.168	.910	.090	.035	.029	.757	.289	7/32	RED GRDDVE
-004	YAES18K-3NK	22-18	#10	RED	.318	.306	.203	.193	.910	.090	.035	.029	.757	.289	7/32	RED GRDDVE
-009	YAES14K-6NK	16-14	#6	BLUE	.256	.244	.152	.142	.774	.114	.035	.029	.652	.221	7/32	BLUE GRDDVE
-010	YAES14K-53NK	16-14	#8	BLUE	.317	.306	.178	.168	.910	.114	.035	.029	.757	.289	7/32	BLUE GRDDVE
-011	YAES14K-8NK	16-14	#10	BLUE	.317	.306	.203	.193	.910	.114	.035	.029	.757	.289	7/32	BLUE GRDDVE
-012	YAES14K-54NK	16-14	1/4	BLUE	.460	.450	.275	.260	1.085	.114	.035	.029	.860	.405	7/32	BLUE GRDDVE
-006	YAES18K-4NK	22-18	5/16	RED	.460	.450	.338	.323	1.090	.090	.035	.029	.865	.406	7/32	RED GRDDVE
-007	YAES18K-5NK	22-18	3/8	RED	.536	.524	.400	.385	1.170	.090	.035	.029	.908	.453	7/32	RED GRDDVE
-001	YAES18K-48NK	22-18	#4	RED	.230	.222	.122	.114	.735	.090	.035	.029	.644	.202	7/32	RED GRDDVE
-005	YAES18K-50NK	22-18	1/4	RED	.460	.450	.275	.260	1.090	.090	.035	.029	.865	.406	7/32	RED GRDDVE
-013	YAES14K-9NK	16-14	5/16	BLUE	.460	.450	.338	.323	1.085	.114	.035	.029	.860	.405	7/32	BLUE GRDDVE
-014	YAES14K-10NK	16-14	3/8	BLUE	.534	.522	.400	.385	1.175	.114	.035	.029	.914	.453	7/32	BLUE GRDDVE
-008	YAES14K-52NK	16-14	#4	BLUE	.256	.244	.122	.114	.774	.114	.035	.029	.652	.221	7/32	BLUE GRDDVE



NOTES:

- ▷ MAXIMUM CABLE INSULATION DIAMETER ACCOMMODATED.
- VOLTAGE RATING: 600V
- OPERATING TEMPERATURE RANGE: -65°C TO 150°C
- MATERIAL: INSULATION- POLYVINYLIDENE FLUORIDE (PVF)
- COLOR-SEE TABLE (LONGITUDINAL STRIPES)
- TERMINAL: HIGH CONDUCTIVITY PURE ELECTROLYTIC COPPER.
- FINISH: TERMINAL-NICKEL PLATED

CONNECTORS SHOWN MEET REQUIREMENTS OF BOEING NORTH AMERICAN, INC. SPEC. 416-0917


TO ORDER BURNDY PRODUCTS CALL 1-800-346-4175
 MANCHESTER, NH 03109, USA
 FOR PRODUCT INFO = <http://www.fciconnect.com>

HIGH TEMP. INSULUG™

ITEM NO: N/A

CAT NO: YAES--K--NK (TABLE)

SCALE: NTS	
DRAWN BY: DBOISVERT	08/08/03
CHECKER: KHENRY	08/08/03
DN APPVL: BDB MACDONALD	08/08/03
MFG APPVL: N/A	--
QC APPVL: CACKERMAN	08/08/03
MKT APPVL: AZVIT	08/07/03
PROD FAN: --	
PROJECT #: --	
DOCUMENT TYPE: SALES	
REL LEVEL: AUTOCAD	



10033202

SHEET 1 OF 1