


DRAWING NO.
10034684

REV.	DATE	DESCRIPTION	ECO	BY	C'K'D.
C	11/06/17	FORMAT CHANGE	47985	JP	MB



NOTES:

- APPROXIMATE AMP RATING: 800 A.
THIS RATING MAY VARY WITH AMBIENT CONDITIONS,
ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.
- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST
MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
- REFERENCE CUSTOMER NUMBER 25-25863-3.

TO ORDER BURNDY® PRODUCTS CALL
 UNITED STATES:
 1-800-346-4175 (LONDONDERRY, NH)
 CANADA:
 1-800-361-6975 (QUEBEC)
 1-800-387-6487 (ALL OTHER PROVINCES)
 FOR PRODUCT INFO: <http://www.burndy.com>

BRAID	
ITEM NO: 10034675	
CAT NO: CB4E13D62G6TN	
SCALE: 1/1	
DRAWN BY: P LAPONIUS	9/29/03
CHECKER: J MICHAUD	9/29/03
DSN APPVL: J MICHAUD	9/29/03
MFG APPVL: --	--
QC APPVL: J BRODEUR	9/29/03
MKT APPVL: D HAMILTON	9/29/03
PROD FAM: --	
PROJECT #: --	SIZE
DOCUMENT TYPE: Sales	C
REL LEVEL: Released	
DRAWING NO	REV
10034684	C
SHEET 1 of 1	

