


DRAWING NO.
10085851

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	2/17/2008 1:12:00 PM	DRAWING RELEASED	15575	RLB	PRL



NOTES:

- APPROXIMATE AMP RATING: 190 INDOOR, 225 OUTDOOR THIS RATING MAY VARY WITH AMBIENT CONDITIONS ORIENTATION OF THE BRAID AND SERVICE CONDITIONS.
- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED, AND ARE FOR REFERENCE ONLY.
- ALL SIZES ARE LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS.
- ALL SIZES ARE LISTED TO CSA (22.2 NO. 41) GROUNDING & BONDING EQUIPMENT STANDARDS.

TO ORDER BURNDY PRODUCTS CALL 1-800-346-4175 MANCHESTER, NH 03109, USA FOR PRODUCT INFO = http://www.fciconnect.com			
BRAID, FLEXIBLE			
ITEM NO: 33216B			
CAT. NO: BD24G203			
DRAWN BY:	R. BOISVERT	02/07/08	
CHECKER:	P. LAPONIUS	02/08/08	
DSN APPVL:	J. PARKER	01/23/08	
MFG APPVL:	L. LEAVITT	01/21/08	
QA APPVL:	J. BRODEUR	01/22/08	
MKT APPVL:	--	--	SCALE: 1:2
PROD FAM:	--	DRAWING NO	REV
PROJECT #:	--	10085851	A
DOCUMENT TYPE:	--	C	SHEET 1 OF 1
REL LEVEL:	Released		

REV: PED200