


DRAWING NO.  
10087796

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	4/18/2008 2:00:00 PM	DRAWING RELEASED	15975	RLB	JP



NOTES:

1. DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED, AND ARE FOR REFERENCE ONLY.
  2. APPROXIMATE AMP RATING: 340 INDOOR, 405 OUTDOOR  
THIS MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.
- 3 ALL SIZES ARE LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS.

TO ORDER BURNDY® PRODUCTS CALL  
 UNITED STATES:  
 1-800-346-4175 (LONDONDERRY, NH)  
 CANADA:  
 1-800-361-6975 (QUEBEC)  
 1-800-387-6487 (ALL OTHER PROVINCES)  
 FOR PRODUCT INFO: <http://www.fciconnect.com>

BRAID	
ITEM NO:	10087402
CAT. NO:	B3G18N1TN
DRAWN BY:	R. BOISVERT 04/18/08
CHECKER:	J. PARKER 04/21/08
DSN APPVL:	J. PARKER 04/07/08
MFG APPVL:	L. LEAVITT 04/07/08
QA APPVL:	J. BRODEUR 04/11/08
MKT APPVL:	P. THERRIEN 04/15/08
SCALE:	3:4
PROD FAM:	--
PROJECT #:	--
DOCUMENT TYPE:	--
REL LEVEL:	Released
DRAWING NO	10087796
REV	A
SHEET	1 OF 1

REV: PED200