


DRAWING NO.
10107789

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	10/15/2009 11:37:00 AM	DRAWING RELEASED	19339	RLB	JP



NOTES:

- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED, AND ARE FOR REFERENCE ONLY.
- APPROXIMATE AMP RATING: 360 INDOOR, 430 OUTDOOR
- ALL SIZES ARE LISTED TO UL467 GROUNDING & BONDING EQUIPMENT STANDARDS.
- ALL SIZES ARE LISTED TO CSA C22.2 NO.41 GROUNDING & BONDING EQUIPMENT STANDARDS.

TO ORDER BURNDY® PRODUCTS CALL
 UNITED STATES:
 1-800-346-4175 (LONDONDERRY, NH)
 CANADA:
 1-800-361-6975 (QUEBEC)
 1-800-387-6487 (ALL OTHER PROVINCES)
 FOR PRODUCT INFO: <http://www.burndy.com>

BRAID	
ITEM NO:	33211J
CAT. NO:	BF 30N
DRAWN BY:	R. BOISVERT 10/15/09
CHECKER:	J. PARKER 10/16/09
DSN APPVL:	J. PARKER 10/14/09
MFG APPVL:	N/A
QA APPVL:	J. BRODEUR 10/13/09
MKT APPVL:	P. THERRIEN 10/13/09
SCALE:	1:2
PROD FAM:	--
PROJECT #:	--
DOCUMENT TYPE:	--
REL LEVEL:	Released
DRAWING NO	10107789
REV	A
SHEET	1 OF 1

REV: PED200