



DRAWING NO.
10108810

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	10/30/2009 1:59:00 PM	DRAWING RELEASED	19431	RLB	JP



- NOTES:
- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED, AND ARE FOR REFERENCE ONLY.
 - APPROXIMATE AMP RATING: 340A INDOOR, 405A OUTDOOR. THIS MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.

TO ORDER BURNDY® PRODUCTS CALL
 UNITED STATES:
 1-800-346-4175 (LONDONDERRY, NH)
 CANADA:
 1-800-361-6975 (QUEBEC)
 1-800-387-6487 (ALL OTHER PROVINCES)
 FOR PRODUCT INFO: <http://www.burndy.com>

BRAID	
ITEM NO:	10108522
CAT. NO:	BE18D58G170TN
DRAWN BY:	R. BOISVERT 10/30/09
CHECKER:	J. PARKER 10/30/09
DSN APPVL:	J. PARKER 10/30/09
MFG APPVL:	--
QA APPVL:	--
MKT APPVL:	--
SCALE:	3:4
PROD FAM:	--
PROJECT #:	--
DOCUMENT TYPE:	--
REL LEVEL:	Released
DRAWING NO	10108810
REV	A
SHEET	1 OF 1

REV: PED200