



DRAWING NO.
10112806

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	3/10/2010 4:17:00 PM	DRAWING RELEASED	20492	RLB	JP



NOTES:

- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED, AND ARE FOR REFERENCE ONLY.
- APPROXIMATE AMP RATING: 190 INDOOR, 225 OUTDOOR
THIS MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.
- ALL SIZES ARE LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS.
- ALL SIZES ARE LISTED TO CSA C22.2 NO. 41 GROUNDING & BONDING EQUIPMENT STANDARDS.



TO ORDER BURNDY® PRODUCTS CALL		BRAID, FLEXIBLE	
UNITED STATES: 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: 10109678	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: BD33D46G26 ITN	
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: R. BOISVERT 03/11/10	
		CHECKER: J. PARKER 03/11/10	
		DSN APPVL: J. PARKER 03/04/10	
		MFG APPVL: C. MARTINEZ 03/09/10	
		QA APPVL: J. BRODEUR 03/09/10	
		MKT APPVL: P. THERRIEN 03/05/10	
		SCALE: 3:4	
		PROD FAM: --	
		DRAWING NO: 10112806	
		REV: A	
		PROJECT #: --	
		SIZE: C	
		DOCUMENT TYPE: --	
		REL LEVEL: Released	
		SHEET 1 OF 1	

REV: PED200