



CATALOG NUMBER	[A]	[B]	[C]	[D]
200LUGP1	2.88IN [73.15MM]	1.90IN [48.26MM]	.225IN [5.72MM]	.625IN [15.88MM]
200LUGP2			.285IN [7.24MM]	.625IN [15.88MM]
200LUGP3			.310IN [7.87MM]	.625IN [15.88MM]
200LUGP4			.360IN [9.14MM]	.625IN [15.88MM]
200LUGP5			.395IN [10.03MM]	.625IN [15.88MM]
200LUGP6			.440IN [11.18MM]	.625IN [15.88MM]
200LUGP7	2.75IN [69.85MM]	1.69IN [42.88MM]	.495IN [12.57MM]	.780IN [19.81MM]
200LUGP8			.550IN [13.97MM]	.780IN [19.81MM]

CATALOG NUMBER	CONDUCTOR SIZE (COPPER OR ALUMINUM)	
	STANDARD OR COMPRESSED	SOLID OR COMPACTED
200LUGP1	6	4
200LUGP2	4	2
200LUGP3	2	1
200LUGP4	1	1/0
200LUGP5	1/0	2/0
200LUGP6	2/0	3/0
200LUGP7	3/0	4/0
200LUGP8	4/0	--

CHARDON
TOLERANCE CHART



HUBBELL® POWER SYSTEMS

CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.

TITLE
200 AMP, 15/25 KV
PROBELOK CONNECTOR

SIZE S	DWG NO. --	CAT / PART / ASSY NO. 200LUGPX	REV 1
-----------	---------------	-----------------------------------	----------

REV DATE 04/25/07	DO NOT SCALE THIS DRAWING	DRN BY JVR	DATE 11/21/06	SHEET 1 OF 1
----------------------	---------------------------	------------	---------------	--------------