

SE208132

CONDUCTOR			BOLT SIZE	CATALOG NO.	FIG. NO.	DIMENSIONS							BURNDY INSTALLATION TOOLING (# CRIMPS)													
FLEX	CODE (AWG)	NAVY				B	C	H	K	L	N	O.D.	T REF.	Z MIN.	DIE INDEX	COLOR CODE	MECHANICAL RATCHET			HYDRAULIC		DIELESS (# CRIMPS)	WIRE STRIP LENGTH			
														MD7-34R	OUR840	YBMRB-1 Y2MR	Y750 Y35 Y39	Y46	Y45							
D	#8 WELD 37/24	#8 AWG	23	#10	YAG8CL-TC10-LD	1	.44 [11]			1.19 [30]	.25 [6]	.27 [7]	.08 [2]	.27 [7]	49	RED	WBCRT (1) WBCVT (1)	XBCRT (1) WBCVT (1)	(1 CRIMP)	UBCRT (1)	UBCRT (1)	UBCRT (1)	MECHANICAL, MY29-11 (1)	1/2"		
					YAG8CL-TC10-LD-45	2	.41 [10]	.68 [17]	.21 [5]	1.20 [30]																
					YAG8CL-TC10-LD-90	3		.80 [20]		.74 [19]																
				1/4	YAG8CL-TC14-LD	1			1.32 [34]	.31 [8]	.08 [2]	.33 [8]														
					YAG8CL-TC14-LD-45	2	.44 [11]	.67 [17]	.27 [7]	1.31 [33]																
					YAG8CL-TC14-LD-90	3		.79 [20]		.86 [22]																
				5/16	YAG8CL-TC516-LD	1			1.38 [35]	.34 [9]	.06 [2]	.36 [9]														
					YAG8CL-TC516-LD-45	2	.52 [13]	.67 [17]	.33 [8]	1.34 [34]																
					YAG8CL-TC516-LD-90	3		.76 [19]		.92 [23]																
				3/8	YAG8CL-TC38-LD	1			1.51 [38]	.41 [10]	.06 [2]	.42 [11]														
					YAG8CL-TC38-LD-45	2	.58 [15]	.66 [17]	.40 [10]	1.45 [37]																
					YAG8CL-TC38-LD-90	3		.75 [19]		1.04 [26]																
1/2	YAG8CL-TC12-LD	1			1.76 [45]	.53 [13]	.05 [1]	.55 [14]																		
	YAG8CL-TC12-LD-45	2	.71 [18]	.66 [17]	.53 [13]	1.67 [42]																				
	YAG8CL-TC12-LD-90	3	.44 [11]	.72 [18]		1.28 [33]																				

SEE SHEET 1 OF 18 FOR NOTES

HYLUG

CAT NO: YAG8CL-TC-LD-
 DRAWN: D FILLION 12-17-92 CHECKED: KAY HENRY 12-18-92
 DESIGN APPR: G PALANI & HENRY 12-30-92 N/A
 S.A. APPR: A LLOYD 12-31-92 MKTS APPR: T NELSON 01-12-93
 CAD FILE: SE208132-SHT02 PW REP: N/A

BURNDY

PROJECT: DD 52410
 DRAWING NO: SE208132
 SHEET 2 of 18

REV.	DATE	DESCRIPTION	BY	C'K'D.

REV. 111991