


DRAWING NO.
SD213079

CATALOG NO.	WIRE RANGE (AWG/kcmil)	L	W	H	HEX KEY	N	M
BIBS2/0-4MT	#14-2/0	4.20 [107]	1.25 [32]	1.50 [38]	3/16	4	6
BIBS2/0-6MT	#14-2/0	5.54 [141]	1.25 [32]	1.50 [38]	3/16	6	8
BIBS2/0-8MT	#14-2/0	6.89 [175]	1.25 [32]	1.50 [38]	3/16	8	10
BIBS2/0-10MT	#14-2/0	8.23 [209]	1.25 [32]	1.50 [38]	3/16	10	12
BIBS2/0-12MT	#14-2/0	9.58 [243]	1.25 [32]	1.50 [38]	3/16	12	14
BIBS250-4MT	#10-250	5.78 [147]	1.95 [49]	2.63 [67]	5/16	4	6
BIBS250-6MT	#10-250	7.65 [194]	1.95 [49]	2.63 [67]	5/16	6	8
BIBS250-8MT	#10-250	9.53 [242]	1.95 [49]	2.63 [67]	5/16	8	10
BIBS250-10MT	#10-250	11.41 [290]	1.95 [49]	2.63 [67]	5/16	10	12
BIBS250-12MT	#10-250	13.28 [337]	1.95 [49]	2.63 [67]	5/16	12	14
BIBS350-4MT	#10-350	5.86 [149]	2.19 [56]	2.63 [67]	5/16	4	6
BIBS350-6MT	#10-350	7.68 [195]	2.19 [56]	2.63 [67]	5/16	6	8
BIBS350-8MT	#10-350	9.50 [241]	2.19 [56]	2.63 [67]	5/16	8	10
BIBS350-10MT	#10-350	11.32 [288]	2.19 [56]	2.63 [67]	5/16	10	12
BIBS350-12MT	#10-350	13.41 [334]	2.19 [56]	2.63 [67]	5/16	12	14
BIBS600-4MT	#4-600	7.84 [199]	2.25 [57]	2.88 [73]	3/8	4	6
BIBS600-6MT	#4-600	10.41 [264]	2.25 [57]	2.88 [73]	3/8	6	8
BIBS600-8MT	#4-600	12.97 [328]	2.25 [57]	2.88 [73]	3/8	8	10
BIBS600-10MT	#4-600	15.53 [394]	2.25 [57]	2.88 [73]	3/8	10	12
BIBS600-12MT	#4-600	18.09 [459]	2.25 [57]	2.88 [73]	3/8	12	14

REV.	DATE	DESCRIPTION	ECO	BY	C.K'D.
0	3/23/01	RELEASED	6390	BM	DB


2 "M" SET SCREW PORTS
PER CONNECTOR (SEE TABLE)



UL LISTED


ALUMINUM SET SCREW
(SEE TABLE FOR HEX SIZE)

ALUMINUM CONNECTOR BODY



"N" WIRE PORTS
PER CONNECTOR (SEE TABLE)

FEATURES	BENEFITS
PLASTISOL COVERED AL6061-TB BODY	SAVES TIME, LOWERS INSTALLATION COSTS, ELIMINATES TAPING.
CLEAR PLASTISOL	ALLOWS VISUAL CONFIRMATION THAT CONDUCTOR IS PROPERLY INSERTED.
OXIDE-INHIBITOR IS PRE-INSTALLED	INHIBITS MOISTURE AND CONTAMINANTS FROM ENTERING THE CONTACT AREA.
RANGE-TAKING	REDUCES THE NUMBER OF CONNECTORS CARRIED IN INVENTORY.



NOTES:

- CONNECTORS ARE SUPPLIED INDIVIDUALLY LABELED. LABEL INFORMATION INCLUDES CATALOG NUMBER, QUANTITY, AND BARCODE.
- END CAPS INSTALLED ON WIRE PORTS AND SET SCREW PORTS.
- ALL CONNECTORS UL LISTED, CSA CERTIFIED FOR ALSCU, 90°C APPLICATIONS.
- DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.

TO ORDER BURNDY PRODUCTS CALL 1-800-346-4175
MANCHESTER, NH 03109, USA
FOR PRODUCT INFO = <http://www.fciconnect.com>

MOUNTED UNITAP™ - PLASTISOL COVERED WIRE CONNECTORS

CAT NO: BIBS--MT (TABLE) SCALE NTS

DRAWN: B. MICHAUD 3/23/01 CHECKED: D. BOISVERT 3/23/01
DSEN APPVL: J. MICHAUD 3/22/01 MFG APPVL: N/A

D.A. APPVL: S. BROWN 3/23/01
MKTG APPVL: N/A
CAD FILE: 50213079-01_0
MOL REF: N/A

BURNDY

DRAWING NO: SD213079 REV 0
SHEET 1 OF 2

REV. 012000