


6. RATED VOLTAGE  $U_r$  12 kV RMS



|        |        |        |       |       |       |
|--------|--------|--------|-------|-------|-------|
| 1.5 kA | 3.0 kA | 5.0 kA | 10 kA | 20 kA | 40 kA |
| 28,1   | 29,5   | 30,9   | 32,3  | 36,3  | 40,7  |

IEC  
CLASS 2  
SURGE  
ARRESTER

|          |            |
|----------|------------|
| REV DATE | 03/10/2023 |
|----------|------------|

CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.

 HUBBELL® POWER SYSTEMS®

|       |                 |
|-------|-----------------|
| TITLE | PVI-LP ARRESTER |
|       | 10.2 kV Uc      |

|      |         |                       |     |
|------|---------|-----------------------|-----|
| SIZE | DWG NO. | CAT / PART / ASSY NO. | REV |
| S    | --      | 214510-C4BC           | 0   |

|                              |            |               |              |
|------------------------------|------------|---------------|--------------|
| DO NOT SCALE<br>THIS DRAWING | DRN BY RVK | DATE 03/10/23 | SHEET 1 OF 1 |
|------------------------------|------------|---------------|--------------|