


NOTE: DUTY CYCLE VOLTAGE RATING - 6 KV RMS

.5 μ SEC IR kV	500 A SWITCHING SURGE IR kV	MAXIMUM 8/20 DISCHARGE VOLTAGE - kV AT					
		1.5 kA	3.0 kA	5 kA	10 kA	20 kA	40 kA
25.0	17.0	19.5	20.5	22.0	24.5	28.5	37.0

CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.	 HUBBELL® POWER SYSTEMS	TITLE ELBOW ARRESTER 5.1 KV MCOV				
		SIZE S	DWG NO. --	CAT / PART / ASSY NO. 215ELA06	REV 0	
REV DATE 07/29/09	DO NOT SCALE THIS DRAWING			DRN BY JVR	DATE 07/29/09	SHEET 1 OF 1