


NOTE: DUTY CYCLE VOLTAGE RATING - 18 KV RMS

.5 μ SEC IR kV	500 A SWITCHING SURGE IR kV	MAXIMUM 8/20 DISCHARGE VOLTAGE - kV AT					
		1.5 kA	3.0 kA	5 kA	10 kA	20 kA	40 kA
67.0	46.0	52.0	56.0	60.0	66.0	78.0	101.0

REV DATE 07/29/09	CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.	 HUBBELL® POWER SYSTEMS			
		TITLE ELBOW ARRESTER 15.3 KV MCOV			
SIZE S	DWG NO. --	CAT / PART / ASSY NO. 215ELA18	REV 0		
DO NOT SCALE THIS DRAWING		DRN BY JVR	DATE 07/29/09	SHEET 1 OF 1	