



DIMENSIONS IN PARENTHESIS ARE METRIC

RATINGS			
MAX CONTINUOUS VOLTAGE		CONTINUOUS CURRENT	
PHASE-TO-GND	PHASE-TO-PHASE		
8.3 kV	14.4 kV	200 AMPERE RMS	
SHORT-TIME CURRENT RATINGS			
0.17-SECOND DURATION		3.00 SECOND DURATION	
10,000 AMPERE RMS SYMMETRICAL		3500 AMPERE RMS SYMMETRICAL	
INSULATION WITHSTAND VOLTAGES			
BASIC IMPULSE LEVEL (1.2X50 MICROSEC. WAVE)	AC-60 HERTZ (ONE MINUTE)	DC (15 MINUTE)	PARTIAL DISCHARGE VOLTAGE (CEV)
95 kV CREST	34 kV RMS	53 kV	<3PC @ 11kV

CHARDON  
TOLERANCE CHART



HUBBELL® POWER SYSTEMS

CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.

TITLE  
INSULATING CAP  
200A 15 KV

SIZE S	DWG NO. --	CAT / PART / ASSY NO. 215ICC	REV 1
-----------	---------------	---------------------------------	----------

REV DATE 03/28/08	DO NOT SCALE THIS DRAWING	DRN BY JVR	DATE 11/18/05	SHEET 1 OF 1
----------------------	---------------------------	------------	---------------	--------------