


NOTES:

- 1) ARRESTERS ARE FOR USE IN TRANSFORMER OIL. THEY WILL OPERATE SATISFACTORY IN WEIGHTED AVERAGE OIL TEMPERATURE OF 90°C (125°C MAX.)
- 2) WEIGHT = 3.50

| | | | | | | | | |
|---|----------|--------|----------|--|--|-----------|-----------------------|---------------|
| 67189 | 10/24/16 | AS | AWR | TOLERANCE CHART 0.0 = ±0.10 0.00 = ±0.030 0.000 = ±0.015 ANGLES = ±30' DO NOT USE FRACTIONS |  HUBBELL® POWER SYSTEMS | | | |
| EC # | DATE | CHG BY | RESP ENG | | TITLE UNDEROIL ARRESTER 17.0 KV MCOV | | | |
| DESC OF DWG: REPLACE 'MADE IN U.S.A.' WITH 'ASSEMBLED IN U.S.A.' — — — REASON (S) FOR CHANGE: — DISPOSITION OF MAT'L: — | | | | CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS. | SIZE | DWG NO. | CAT / PART / ASSY NO. | REV |
| | | | | | A | 021482-00 | 221117-3002 | 2 |
| | | | | | DO NOT SCALE THIS DRAWING | | DRN BY MAJ | DATE 01/16/00 |