


NOTE: DUTY CYCLE VOLTAGE RATING - 9 KV RMS

.5 $\mu$ SEC IR kV	5kA kV	500 A SWITCHING SURGE IR kV	MAXIMUM 8/20 DISCHARGE VOLTAGE - kV AT					
			1.5 kA	3.0 kA	5 kA	10 kA	20 kA	40 kA
33.5		23.0	26.0	28.0	30.0	33.0	39.0	50.5

CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.	 <b>HUBBELL® POWER SYSTEMS</b>	TITLE <b>ELBOW ARRESTER 7.65 KV MCOV</b>		SIZE <b>S</b>	DWG NO. <b>--</b>	CAT / PART / ASSY NO. <b>225ELA09</b>	REV <b>0</b>
		DO NOT SCALE THIS DRAWING		DRN BY JVR	DATE 09/23/09	SHEET 1 OF 1	

REV DATE 09/23/09