


NOTE: DUTY CYCLE VOLTAGE RATING - 24 KV RMS

.5 μ SEC IR kV	5kA kV	500 A SWITCHING SURGE IR kV	MAXIMUM 8/20 DISCHARGE VOLTAGE - kV AT					
			1.5 kA	3.0 kA	5 kA	10 kA	20 kA	40 kA
92.0		63.0	71.5	76.5	82.0	90.5	106.5	138.0

		 HUBBELL® POWER SYSTEMS				
	CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.		TITLE ELBOW ARRESTER 19.5 KV MCOV			
REV DATE 09/01/09		SIZE S	DWG NO. --	CAT / PART / ASSY NO. 235ELA24	REV 0	
		DO NOT SCALE THIS DRAWING	DRN BY JVR	DATE 09/01/09	SHEET 1 OF 1	