


NOTE: DUTY CYCLE VOLTAGE RATING - 30 KV RMS

.5μ SEC IR KV	500 A SWITCHING SURGE IR KV	MAXIMUM 8/20 DISCHARGE VOLTAGE - KV AT					
		1.5 kA	3.0 kA	5 kA	10 kA	20 kA	40 kA
98	70	79	84	89	101	116	145

<p>CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.</p>				<h1>HUBBELL® POWER SYSTEMS</h1>			
		<p>TITLE</p> <h2>ELBOW ARRESTER 24.0 KV MCOV</h2>					
<p>REV DATE</p> <p>06/19/17</p>		<p>SIZE</p> <p>S</p>	<p>DWG NO.</p> <p>--</p>	<p>CAT / PART / ASSY NO.</p> <p>236ELA30</p>		<p>REV</p> <p>0</p>	
		<p>DO NOT SCALE THIS DRAWING</p>	<p>DRN BY BvB</p>	<p>DATE 06/19/17</p>	<p>SHEET 1 OF 1</p>		