



- NOTES:
 1. ALL DIMENSIONS ARE IN INCHES AND [MILLIMETERS]
 2. BOX VOLUME: 30.3 IN³ [496.5 CM³]
 3. UL LISTED

KNOCKOUTS		
TRADE SIZE	LOCATION	QTY.
(1/2"-3/4") TKO®	B, D	1
1/2" KO	B, D	2
1/2" KO	E	1

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
SPACER	STEEL	GALVANIZED
SIDE	STEEL	GALVANIZED
CLAMPS	STEEL	GALVANIZED
FASTENERS	STEEL	GALVANIZED

248 CUS

INITIAL RELEASE	RMV	01-02-18	
SYM.	REVISION DESCRIPTION	APP	DATE

248

DIMENSION SHEET FOR CAT. NO.

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE:
4" SQ. BOX, 2-1/8" DP., 1/2"-3/4" KO'S, W/ MC CLAMPS

TOLERANCE UNLESS OTHERWISE SPECIFIED

RACO
 South Bend, Indiana

.XX DECIMAL ±.015
 .XXX DECIMAL ±.005
 ANGLE ±2°

DRAWN BY:	RMV	SCALE:
APP. BY:	N.S.	1:3
DATE:	01-02-18	

SIZE:

A

11in*17in