


\*\*\* BILL OF MATERIAL \*\*\*

PT NO.	CATALOG NO.	QTY	DESCRIPTION
1	PATCASELI	1	CASE, TOOL PATRIOT LITHIUM-ION
2	BAT18VLI	2	BATTERY, LITHIUM ION 18V
3	PATCHGRLI	1	CHARGER, BATTERY LITHIUM ION
4	BATCHGRLIOMI	1	BATTERY CHARGER SAFETY OPERATING MAINTENANCE & INSTRUCTIONS
5	PT208620	1	LANYARD
6	PAT4PC834LIOMI	1	SOMI, PAT4PC834LI 
7	PT20443801	1	FIVE YEAR WARRANTY CARD
8	LIMSDS	1	MSDS, LITHIUM-ION BATTERY

CATALOG NUMBER	DESCRIPTION	CHARGER CATALOG NO.
PAT4PC834-LI	PATRIOT®4PC834 WITH 120V CHARGER	PATCHGRLI
PAT4PC834-LIDC	PATRIOT®4PC834 WITH 12V CHARGER	PATCHGRLI DC

SPECIFICATIONS:

OUTPUT FORCE: 6 TONS (5.4 METRIC TONS)  
 TOOL WEIGHT WITH BATTERY: 13.2 LBS (5.9 kg)  
 LENGTH: 15.6 IN (39.6 cm)  
 WIDTH: 3.2 IN (8.1 cm)  
 HEIGHT: 14.1 IN (35.8 cm)  
 OPERATING VOLTAGE: 18V-DC  
 RECHARGE TIME: 30 MINUTES

FOR USE ON:

COPPER: #8 - 1000 kcmil  
 COPPER: #8 - 500kcmil  
 COPPER FLEX: #8 - 777.7 kcmil FLEX (750 NOMINAL)  
 ALUMINUM: #8 - 750 kcmil  
 ALUMINUM: #8 - 750 kcmil

TERMINALS: YA, YA-L  
 SPLICES: YS, YS-L, YS-T, YS-R  
 TERMINALS: YA-FX, YA-V  
 TERMINALS: YA-L-FX  
 SPLICES: YS, YS-LB, YSV-FXB  
 TERMINALS: YA-A  
 SPLICES: YS-A  
 HYPLUG AYP, AYPO


FEATURES AND BENEFITS

- REFINED HYDRAULIC SYSTEM FOR ULTRA PERFORMANCE, SPEED AND RELIABILITY.
- FIELD PROVEN ELECTRONICS FOR ULTIMATE RELIABILITY IN THE HARSHTEST ENVIRONMENTS.
- OVERMOLDED HANDLE FOR COMFORT AND IMPROVED GRIP; ALLOWS FOR ONE HANDED OPERATION FOR ADVANCE RETRACT AND HOLD.
- MAKITA 18 VOLT LITHIUM-ION BATTERIES PROVIDE 2.5 TIMES MORE CHARGE/DISCHARGE CYCLES THAN TRADITIONAL Ni-Cd BATTERIES AND PROVIDE 430% MORE LIFETIME WORK.
- MAKITA 30 MINUTE CHARGER CONTROLS CURRENT, VOLTAGE AND TEMPERATURE TO MAXIMIZE BATTERY LIFE.
- FORCED AIR COOLING FAN COOLS THE BATTERY BY FORCING COOL AIR THROUGH THE BATTERY'S BUILT IN AIR VENTS.
- DIELESS SYSTEM ELIMINATES THE NEED TO PURCHASE AND MAINTAIN DIES.
- DIELESS SYSTEM ALLOWS CONNECTORS AND SPLICES TO BECOME RANGE TAKING.
- C-SHAPED HEAD DESIGN ROTATES 360° AND ALLOWS FOR EASY REMOVAL ON CONTINUOUS CONDUCTORS.
- ERGONOMICALLY BALANCED TOOL DESIGN EASES OPERATION AND HELPS LESSEN FATIGUE.
- DURABLE HIGH IMPACT FORMED CARRYING CASE PROVIDES SUPERIOR PROTECTION AND STORES ALL ACCESSORIES.
- 5 YEAR LIMITED WARRANTY ON THE TOOL.
- LIFETIME WARRANTY ON INFINITY DRIVE .
- 3 YEAR LIMITED WARRANTY ON THE BATTERIES AND CHARGER.

NOTES:

 READ AND FOLLOW ALL INSTRUCTIONS PROVIDED BY THE OPERATORS MANUAL AND WARNING LABEL BEFORE USING THIS TOOL.

REV.	DATE	DESCRIPTION	ECO	BY	C'H'K.
C	2018-09-06 00:00:00 EDT	UPDATED AS PER MARKUP	49802	RS	RM



- TOOL ACCEPTS 18V MAKITA LITHIUM ION BATTERIES, BL SERIES OF SIZE 2.0 AHR AND GREATER IF THE PLASTIC BATTERY CLIP IN THE TOOL HAS A "STAR" MOLDED INTO IT. THE "STAR" IDENTIFIES ACCEPTANCE OF THE BL SERIES BATTERIES.
- FOR TOOLS WHICH DO NOT HAVE A "STAR" MOLDED INTO THE PLASTIC BATTERY CLIP, USE IS LIMITED TO THE BL 1830 (3.0 AHR) BATTERY. FORCING ANY OTHER BATTERY INTO THIS TOOL WILL VOID THE WARRANTY.



TO ORDER BURNDY® PRODUCTS CALL  
 UNITED STATES:  
 1-800-346-4175 (LONDONDERRY, NH)

CANADA:  
 1-800-361-6975 (QUEBEC)  
 1-800-387-6487 (ALL OTHER PROVINCES)  
 FOR PRODUCT INFO: <http://www.burndy.com>

PATRIOT® 4 POINT C-HEAD DIELESS TOOL

ITEM NO: --	CAT. NO: SEE TABLE		
DRAWN BY: T. FAUCHER 06/10/2010	CHECKER: M. CHIASSON 10/27/2010		
DSN APPVL: M. CHIASSON 10/27/2010	MFG APPVL: S. GONYAW 10/27/2010		
QA APPVL: J. BRODEUR 10/27/2010	MKT APPVL: R. POIRIER 10/28/2010		
PROJ FAM: TOOLS, BATTERY	SIZE	DRAWING NO	REV
PROJECT #: 14074	B	30003020	C
DOCUMENT TYPE: Sales		SHEET 1 OF 1	
REL LEVEL: Released			