


DRAWING NO.
30008316

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	12/6/2010 12:00:00 AM	DRAWING RELEASED	22854	MG	RM

REV: PE0200



FERRULES: MATERIAL: COPPER
(2 PER ASSEMBLY)

BRAID: MATERIAL: TINNED COPPER
(1 PER ASSEMBLY)

NOTES:

- APPROXIMATE AMP. RATING: 290A THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.
 - DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
- 3 ALL SIZES ARE LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS.
- 4 ALL SIZES ARE LISTED TO CSA C22.2 NO.41 GROUNDING & BONDING EQUIPMENT STANDARDS.

TO ORDER BURNDY® PRODUCTS CALL		BRAID, FLEXIBLE	
UNITED STATES: 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: 30006035	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: BB100L30N	
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: B. SURESH BABU 11/04/10	
		CHECKER: J. MICHAUD 12/07/2010	
		DSN APPVL: J. MICHAUD 12/07/2010	
		MFG APPVL: --	
		QA APPVL: J. BRODEUR 12/14/2010	
		MKT APPVL: P. THERRIEN 12/08/2010	
		SCALE: 5:8	
		PROD FAM: MECHANICAL GROUNDING	
		DRAWING NO: 30008316	
		REV: A	
		PROJECT #: --	
		SIZE: C	
		DOCUMENT TYPE: Sales	
		REL LEVEL: Released	

