

DRAWING NO.  
30009427

CATALOG NO.	ITEM NO.	CU. CONDUCTOR RANGE	INSULATION COLOR	INSULATION TYPE	NEMA TAB	B	W	L
FLNI825X03D	30008984	22 AWG - 18 AWG	RED	NYLON	.25 X .032	.40 [10]	.25 [6]	.60 [15]
FLNI425X03D	30008985	16 AWG - 14 AWG	BLUE	NYLON	.25 X .032	.40 [10]	.25 [6]	.63 [16]
FLNI025X03D	30008986	12 AWG - 10 AWG	YELLOW	NYLON	.25 X .032	.40 [10]	.25 [6]	.64 [16]

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
B	12/15/2011 00:00:00 AM	UPDATED AS PER ECO MARKUP	26299	AD	MA

D

D

C

C

B





B

A

A

REV: PE0200

NOTE:  
1. DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS  
ROUNDED OFF TO THE NEAREST MILLIMETER,  
UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.



TO ORDER BURNDY® PRODUCTS CALL  
UNITED STATES:  
1-800-346-4175 (LONDONDERRY, NH)  
CANADA:  
1-800-361-6975 (QUEBEC)  
1-800-387-6487 (ALL OTHER PROVINCES)  
FOR PRODUCT INFO: <http://www.burndy.com>

QUICK DISCONNECT FLAG		
ITEM NO: SEE TABLE		
CAT. NO: SEE TABLE		
DRAWN BY: P. SRIDHAR 12/10/2010	<b>BURNDY</b>	
CHECKER: K. BOUTIN 03/08/2011		
DSN APPVL: K. BOUTIN 03/08/2011		
MFG APPVL: P. KEENAN 03/08/2011		
QA APPVL: C. KOWALCZYK 03/10/2011		
MKT APPVL: J. SYLVIA 03/09/2011	SCALE: 1:1	
PROD FAM: --	DRAWING NO	REV
PROJECT #: --	30009427	B
DOCUMENT TYPE: Sales	SHEET 1 OF 1	
REL LEVEL: Released		

4

3

2

1