





DRAWING NO.  
30009580

CATALOG NO.	ITEM NO	CU CONDUCTOR ACCOMMODATED	COLOR	W	L
TTVI8	30009047	22 AWG-18 AWG	RED	.38 [10]	.72 [18]
TTVI4	30009048	16 AWG-14 AWG	BLUE	.38 [10]	.72 [18]
TTVI0	30009049	12 AWG-10 AWG	YELLOW	.38 [10]	.72 [18]

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
B	12/15/2011 00:00:00 AM	UPDATED AS PER ECO MARKUP	26299	AD	MA



NOTE:

1. DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS  
ROUNDED OFF TO THE NEAREST MILLIMETER,  
UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.

TO ORDER BURNDY® PRODUCTS CALL  
UNITED STATES:  
1-800-346-4175 (LONDONDERRY, NH)  
CANADA:  
1-800-361-6975 (QUEBEC)  
1-800-387-6487 (ALL OTHER PROVINCES)  
FOR PRODUCT INFO: <http://www.burndy.com>

T-TAP CONNECTORS			
ITEM NO: SEE TABLE			
CAT. NO: SEE TABLE			
DRAWN BY: N.D.KANNAN 12/15/2010	SCALE: 3:1		
CHECKER: K.BOUTIN 03/08/2011	DRAWING NO		
DSN APPVL: K.BOUTIN 03/08/2011	30009580		
MFG APPVL: P.KEENAN 03/08/2011	REV		
QA APPVL: C.KOWALCZYK 03/10/2011	B		
MKT APPVL: J.SYLWIA 03/09/2011	SHEET 1 OF 1		
PROD FAM: CM&R COMPRESSION	PROJECT #		
PROJECT #: --	SIZE		
DOCUMENT TYPE: Sales	C		
REL LEVEL: Released	B		

REV: PE0200

D  
C  
B  
A

D  
C  
B  
A

4 3 2 1