REV.	DATE	DESCRIPTION	ECO	BY	C'H'K.
B	3/30/2011 1:00:00 AM	add to note #5 SUITABLE FOR CONDUCTOR TEMPERTURE OF 250 °C	23978	DDD	RD



NOTES:

1. MATERIAL:
   - CONNECTOR, 356 CAST ALUMINUM ALLOY
   - BOLT ALUMINUM ALLOY, SELF TIGHTENING TORQUE

2. DIMENSIONS IN BRACKETS [ ] DENOTE METRIC UNITS [SI UNITS] AND ARE ROUNDED TO THE NEAREST WHOLE NUMBER. UNLESS OTHERWISE SPECIFIED THESE UNITS SHALL BE USED FOR REFERENCE ONLY.

3. PROVIDED WITH 3/4" BREAK-AWAY HARDWARE
   TIGHTEN UNTIL HEAD SHEARS OFF.
   RECOMMEND A 12" RATCHET WITH DEEP SOCKET.

4. CONNECTOR SHALL BE SHIPPED PRE-ASSEMBLED.

5. 345 KV MAXIMUM VOLTAGE. SUITABLE FOR CONDUCTOR TEMPERTURE OF 250 °C

REV: PE0200

TO ORDER BURNDY® PRODUCTS CALL

UNITED STATES:
1-800-346-4175 (LONDONDERRY, NH)

CANADA:
1-800-361-6975 (QUEBEC)
1-800-387-6487 (ALL OTHER PROVINCES)

FOR PRODUCT INFO: http://www.burndy.com

HITEMP SPACER

ITEM NO: 30012140

CAT. NO: S2GBP463ASG

DRAWN BY: DD	3/24/11	
CHECKER: B.D.	3/24/11	
DSN APPVL: R.DEFRANCE	3/28/11	
MFG APPVL: --	--	
QA APPVL: J.BRODEUR	--	
MKT APPVL: D.HAMILTON	3/24/11	SCALE: 1:1
PROD FAM: --		DRAWING NO: 30013742
PROJECT #: --	SIZE: B	REV: B
DOCUMENT TYPE: --		SHEET 1 OF 1
REL LEVEL: Released		