




DRAWING NO.
30021690

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	10/28/2011 00:00:00 AM	CREATE SALES DRAWING FOR BB024L12G18	25974	BSB	MA



SCALE 1:1

- NOTES:
1. APPROXIMATE AMP. RATING: 93A. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF BRAID, AND OTHER SERVICE CONDITIONS.
 2. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.

TO ORDER BURNDY® PRODUCTS CALL		BRAID, FLEXIBLE	
UNITED STATES: 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: 332765	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: BB024L12G18	
FOR PRODUCT INFO: http://www.burndy.com		DRAWN BY: B.SURESH BABU 10/28/11	
		CHECKER: E.MARTIN 10/28/11	
		DSN APPVL: E.MARTIN 10/28/11	
		MFG APPVL: --	
		QA APPVL: C.ACKERMAN 11/11/11	
		MKT APPVL: P.THERRIEN 10/28/11	
		SCALE: 1:1	
		PROD FAM: CM&R COMPRESSION	
		DRAWING NO: 30021690	
		REV: A	
		PROJECT #: --	
		SIZE: C	
		DOCUMENT TYPE: Sales	
		REL LEVEL: Released	
		SHEET 1 OF 1	

REV: PE0200