


CATALOG NUMBER	ITEM NUMBER	L
B2D12G63W	002665	12.00 [305]
B2D36G63W	002664	36.00 [914]
B2D40G63W	002661	40.00 [1016]
B2D45G63W	002660	45.00 [1143]
B2D48G63W	002666	48.00 [1219]
B2D52G63W	002667	52.00 [1321]
B2D65G63W	002662	65.00 [1651]
B2D72G63W	002663	72.00 [1829]

REV.	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	01/05/2011 00:00:00 AM	SALES DRAWING FOR B2D--G63W BRAIDS	26466	BT	MA



- NOTES:
- APPROXIMATE AMP. RATING: 380A INDOOR, 455A OUTDOOR
THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID AND OTHER SERVICE CONDITIONS.
 - DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
 - ALL SIZES ARE LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS.
 - ALL SIZES ARE LISTED TO CSA C22.2 NO.41 GROUNDING & BONDING EQUIPMENT STANDARDS.
 - SUFFIX "W" DENOTES HOT TIN DIPPED FERRULES.

TO ORDER BURNDY® PRODUCTS CALL		BRAID	
UNITED STATES:		ITEM NO: SEE TABLE	
1-800-346-4175 (LONDONDERRY, NH)		CAT. NO: B2D--G63W (TABLE)	
CANADA:		DRAWN BY: T.BALAN 1/05/2012	
1-800-361-6975 (QUEBEC)		CHECKER: M.EVAN 1/06/2012	
1-800-387-6487 (ALL OTHER PROVINCES)		DSN APPVL: M.EVAN 1/06/2012	
FOR PRODUCT INFO: http://www.burndy.com		MFG APPVL: --	
		QA APPVL: K.CHERYL 1/12/2012	
		MKT APPVL: T.PETER 1/06/2012	
		SCALE: 1:1	
		DRAWING NO	
		PROJECT #: --	
		SIZE	
		DOCUMENT TYPE: Sales	
		REL LEVEL: Released	
		DRAWING NO	
		30023634	
		SHEET 1 OF 1	
		REV	
		A	

REV: PE0200