

DESIGN CHARACTERISTICS

DRY ARC DISTANCE	23 IN
LEAKAGE DISTANCE	54 IN
60 Hz DRY FLASHOVER	255 kV
60 Hz DRY WITHSTAND	245 kV
60 Hz WET FLASHOVER	190 kV
60 Hz WET WITHSTAND	175 kV
IMPULSE CRITICAL POSITIVE	420 kV
IMPULSE CRITICAL NEGATIVE	435 kV
MAX. RIV AT 1000 kHz	10 μV
RIV TEST VOLTAGE	32 kV
POWER ARC	150 kA CYCLES
NET WEIGHT	5 LBS
TENSION PROOF TEST	10,000 LBS
ULTIMATE TENSION STRENGTH	15,000 LBS
NO. OF WEATHERSHEDS	8

HUBBELL/THE OHIO BRASS CO.

8711 WADSWORTH ROAD, WADSWORTH, OHIO

PART NAME: VERI LITE SUSPENSION INS / 405004-1301			SCALE .25=1
DESIGN JDS	DATE 09/29/95	DWG. NO. S011321-00	REV. NO. 04
DRAWN JVR	DATE 09/24/96		

Approved 10-02-1996

905