


REV	DATE	DESCRIPTION	ECO	BY	CHK.
A	05/22/2012	CREATE SALES DRAWING	27597	BT	MA



NOTES:

1. APPROXIMATE AMP RATING: 1000A INDOOR, 1200A OUTDOOR. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.

2. DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.

3. SUFFIX "TN" DENOTES TIN PLATING.

4. LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS.

TO ORDER BURNDY PRODUCTS CALL		BRAID	
UNITED STATES		ITEM NO: 50000663	
1-800-346-4175 (LONDONDERRY, NH)		CAT. NO: B4F12G83TN	
CANADA:		DRAWN BY: E.MARTIN 5/22/2012	
1-800-361-6975 (QUEBEC)		CHECKER:	
1-800-387-6487 (ALL OTHER PROVINCES)		DSN APRVL: E.MARTIN 5/22/2012	
FOR PRODUCT INFO: <a href="http://www.burndy.com">http://www.burndy.com</a>		MFG APRVL: M.JOEL 5/28/2012	
		QA APRVL: R.CATHLEEN 5/29/2012	
		MKT APRVL: R.CATHLEEN 5/29/2012	
		PROJ FAM: MECHANICAL GROUNDING	
		PROJECT #: _____	
		DRAWING NO	
		50000664	
		REV	
		A	
		SHEET 1 OF 1	
		REL LEVEL: Released	