


REV	DATE	DESCRIPTION	ECO	BY	CH'K.
A	09/24/2012	INITIAL RELEASE	28921	TR	EM



NOTES:

1. APPROXIMATE AMP RATING: 340A INDOOR, 405A OUTDOOR. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.
2. DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
- 3 ALL SIZES ARE LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS.
- 4 ALL SIZES ARE LISTED TO CSA 22.2 NO.41 GROUNDING & BONDING EQUIPMENT STANDARDS.

TO ORDER BURNDY PRODUCTS CALL		BRAID	
UNITED STATES		ITEM NO: 50009121	
1-800-346-4175 (LONDONDERRY, NH)		CAT. NO: BE20G196	
CANADA:		DRAWN BY: B.DURATCHAMY 9/18/2012	
1-800-361-6975 (QUEBEC)		CHECKER: E.MARTIN 9/27/2012	
1-800-387-6487 (ALL OTHER PROVINCES)		DSN APRVL: E.MARTIN 9/27/2012	
FOR PRODUCT INFO: http://www.burndy.com		MFG APRVL: --	
		QA APRVL: J.MEDINA 9/28/2012	
		MKT APRVL: K.ROBICHEAU 9/27/2012	
		PROJ FAM: MECHANICAL GROUNDING	
		PROJECT #: _____	
		DRAWING NO	
		50009122	
		REV	
		A	
		DOCUMENT TYPE: SALES	
		REL LEVEL: Released	
		SIZE	
		B	
		SHEET 1 OF 1	