




REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	08/01/2013	NEW SALES DRAWING CREATION	32615	MVP	MB



NOTES:

- APPROXIMATE AMP RATING: 190A INDOOR, 225A OUTDOOR. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.
- DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.

TO ORDER BURNDY® PRODUCTS CALL		BRAID	
UNITED STATES		ITEM NO: GB1003B	
1-800-346-4175 (LONDONDERRY, NH)		CAT. NO: GB1003B	
CANADA:		DRAWN BY: MANIMEKALA 08/01/2013	
1-800-361-6975 (QUEBEC)		CHECKER: T REYNOLDS 08/16/2013	
1-800-387-6487 (ALL OTHER PROVINCES)		DSN APRVL: L TROMBLEY 08/20/2013	
FOR PRODUCT INFO: <a href="http://www.burndy.com">http://www.burndy.com</a>		MFG APRVL: M STEVENS 08/17/2013	
		QA APRVL: J BRODEUR 08/19/2013	
		MKT APRVL: K ROBICHEAU 08/19/2013	
PROD FAM: MECHANICAL GROUNDING	DRAWING NO	REV	
PROJECT #: --	50029515	A	
DOCUMENT TYPE: SALES	SIZE	SHEET 1 OF 1	
REL LEVEL: Released	B		