



REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	10/08/2013	DRAWING UPDATED AS PER MARK UP	33569	VK	PB



NOTES:

- APPROXIMATE AMP RATING: 340A INDOOR, 403A OUTDOOR. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS.
- DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
- LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS.
- LISTED TO CSA 22.2 NO.41 GROUNDING & BONDING EQUIPMENT STANDARDS.



TO ORDER BURNDY® PRODUCTS CALL		BRAID	
UNITED STATES 1-800-346-4175 (LONDONDERRY, NH)		ITEM NO: 50032124	
CANADA: 1-800-361-6975 (QUEBEC) 1-800-387-6487 (ALL OTHER PROVINCES)		CAT. NO: BF22D25G27	
FOR PRODUCT INFO: <a href="http://www.burndy.com">http://www.burndy.com</a>		DRAWN BY: MANIMEKALA 09/27/2013	
		CHECKER: T REYNOLDS 10/08/2013	
		DSN APRVL: T REYNOLDS 10/08/2013	
		MFG APRVL: M STEVENS 10/09/2013	
		QA APRVL: C LINDQUIST 10/09/2013	
		MKT APRVL: K ROBICHEAU 10/08/2013	
		PROD FAM: --	
		PROJECT #: --	
		DOCUMENT TYPE: SALES	
		REL LEVEL: Released	
		SIZE	
		B	
		DRAWING NO	
		50032827	
		REV	
		A	
		SHEET 1 OF 1	