


REV	DATE	DESCRIPTION	ECO	BY	CHK.
A	11/26/2014	DRAWING RELEASED	38309	MS	MB



NOTES:

1. MATERIAL: FERRULES: COPPER HOT TIN DIPPED  
BRAID: TINNED COPPER
2. CURRENTS PROVIDED ARE BASED ON A 30°C RISE OVER AMBIENT TEMPERATURE. THIS RATING MAY VARY WITH AMBIENT CONDITIONS, ORIENTATION OF THE BRAID, AND OTHER SERVICE CONDITIONS. APPROX AMP RATING: 360 INDOOR, 430 OUTDOOR.
3. DIMENSIONS IN BRACKETS [ ] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE NOTED, AND ARE FOR REFERENCE ONLY.
- 4 LISTED TO UL 467 GROUNDING & BONDING EQUIPMENT STANDARDS.
- 5 LISTED TO CSA 22.2 NO.41 GROUNDING & BONDING EQUIPMENT STANDARDS.
6. APPROXIMATE WEIGHT: 4.560 LBS

TO ORDER BURNDY® PRODUCTS CALL		FLEXIBLE BRAID JUMPER	
UNITED STATES		ITEM NO: 50052412	
1-800-346-4175 (LONDONDERRY, NH)		CAT. NO: BF22G93W	
CANADA:		DRAWN BY: KINGULAS	25-12-2014
1-800-361-6975 (QUEBEC)		CHECKER: BAWANIKANDAN	25-12-2014
1-800-387-6487 (ALL OTHER PROVINCES)		DSN APRVL: L.TRONBLEY	12-12-2014
FOR PRODUCT INFO: <a href="http://www.burndy.com">http://www.burndy.com</a>		DESIGNER: S. PATTREY	12-12-2014
		QA APRVL: S. PATTREY	12-12-2014
		MKT APRVL: K.RCBC/HEAU	14-11-2014
PROJECT #:	SALES	SIZE	
RELIEVED:	Released	B	
DRAWING NO	50052413		
REV	A		